



## Eaton 811023FULL-0039

Eaton, Alarms & signalling devices, Fulleon, Solista Maxi LED beacon, Clear Lens, Red flash, White housing, Shallow white (W1) base, White PCB (SOLX/RF/CL/W1/S RED FLASH (WHITE RESIST))

### □□□□

|                             |                                 |
|-----------------------------|---------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Solista Fire alarm beacon |
| <b>CATALOG NUMBER</b>       | 811023FULL-0039                 |
| <b>PRODUCT LENGTH/DEPTH</b> | 53 mm                           |
| <b>PRODUCT HEIGHT</b>       | 93 mm                           |
| <b>PRODUCT WIDTH</b>        | 93 mm                           |
| <b>PRODUCT WEIGHT</b>       | 0.1 kg                          |
| <b>COMPLIANCES</b>          | EN 50130-4:2011                 |
| <b>CERTIFICATIONS</b>       | Not Applicable                  |

□□□□

□□

|                                 |                                |
|---------------------------------|--------------------------------|
| NOMINAL VOLTAGE                 | 24 V                           |
| VOLTAGE TYPE                    | DC                             |
| ELECTRICITY CONSUMPTION         | 0.011 A                        |
| POWER                           | 0.4 W                          |
| LENS COLOR                      | Clear                          |
| MATERIAL HOUSING                | Plastic                        |
| COLOR HOUSING                   | White                          |
| MOUNTING METHOD                 | Surface mounting               |
| NUMBER OF MODES                 | 9                              |
| STANDBY-TIME UP TO              | 0 hour                         |
| AMBIENT TEMPERATURE - MAX       | 55 °C                          |
| AMBIENT TEMPERATURE - MIN       | -10 °C                         |
| LAMP TYPE                       | LED not exchangeable           |
| LAMP HOLDER                     | Other                          |
| DEGREE OF PROTECTION (IP)       | IP21                           |
| ADDRESSING MODE                 | Hard addressing                |
| ALARM CURRENT - MAX             | 22 mA                          |
| ALARM CURRENT - MIN             | 3 mA                           |
| CONSTRUCTION MATERIAL           | ABS/FR                         |
| HUMIDITY (NON CONDENSING) - MAX | 95 %                           |
| HUMIDITY (NON CONDENSING) - MIN | 0 %                            |
| OPERATING TEMPERATURE - MAX     | 55 °C                          |
| OPERATING TEMPERATURE - MIN     | -10 °C                         |
| STANDBY CURRENT                 | 0                              |
| SYSTEM TYPOLOGY                 | Conventional (Non-addressable) |
| PRODUCT BRANDING                | Eaton                          |
| NOMINAL VOLTAGE - MIN           | 12 V                           |
| NOMINAL VOLTAGE - MAX           | 48 V                           |
| ELECTRICITY CONSUMPTION - MIN   | 0.01 A                         |
| ELECTRICITY CONSUMPTION - MAX   | 0.013 A                        |
| INTEGRATED FUNCTION             | Continuous Light               |

|                   |                                                |
|-------------------|------------------------------------------------|
|                   | Flashlight                                     |
| CABLE ENTRY       | Rear                                           |
| MOUNTING POSITION | Wall (weatherproof)<br>Wall surface (internal) |
| LIGHT COLOR       | Red                                            |
| SYSTEM WIRING     | 0.5 - 2.5 mm                                   |

|  |
|--|
|  |
|  |
|  |
|  |