



Eaton 93PX15KIRTN

Eaton 93PX 15 kW RT9U Netpack. Includes 15 kW PM, 1 set of EBM, Network card and rail kits.

□□□□

PRODUCT NAME	Eaton 93PX UPS
CATALOG NUMBER	93PX15KIRTN
PRODUCT LENGTH/DEPTH	820 mm
PRODUCT HEIGHT	128 mm
PRODUCT WIDTH	600 mm
PRODUCT WEIGHT	157.9 kg
COMPLIANCES	CE Marked RoHS Compliant CB
CERTIFICATIONS	IEC/EN 62040-2 IEC/EN 62040-1 EN 62040-3 Manufactured in a plant certified to ISO 9001 and ISO 14001 management system standards



Powering Business Worldwide

AUDIBLE ALARMS	Yes
AUTO SHUTDOWN FUNCTION	Yes
INTERNAL BATTERY INCLUDED	Yes
USER REPLACABLE BATTERIES	No
BATTERY CHARGER TYPE	ABM technology
EXTERNAL BATTERY CONNECTION	Hardwired
COLOR	Black
COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Dry contacts (4 outputs, relay, DB9) • DB15 for parallel operation
CONSTRUCTION TYPE	482.6 mm (19 inch) device
EFFICIENCY (ECO-MODE)	99 %
IMPROVED EFFICIENCY MODE	ESS
NUMBER OF COMMUNICATION SLOTS	1
FEED TYPE	AC
FORM FACTOR	Rack/tower
HOT-SWAPPABLE POWER MODULES	No
INPUT CONNECTION	Fixed connection
INPUT NOMINAL VOLTAGE	380Y/220V nominal (400V/230V, 415Y/240V)
NUMBER OF OUTPUT CONNECTIONS C13	0
NUMBER OF OUTPUT CONNECTIONS C19	0
NUMBER OF OUTPUT CONNECTIONS FIXED CONNECTION	1
OUTPUT FREQUENCY	50 Hz (50/60 Hz programmable)
OUTPUT POWER FACTOR	1
OVERALL EFFICIENCY	0.96 %

PACKAGE CONTENTS	• UPS • EBM • Network card • Rail kit (x3) • Quickstart guide • Safety instructions
PARALLELEABLE	Parallel for capacity and redundancy
NUMBER OF PARALLEL UNITS	3
PHASE (INPUT)	3
PHASE (OUTPUT)	3
POTENTIAL FREE SWITCH CONTACT	No
RACK SIZE	9U
RUNTIME GRAPH	View runtime graph
SNMP	Yes
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
TOPOLOGY	Online
KVA RATING	15 kVA
WATTAGE	15 kW
NUMBER OF OUTPUT CONNECTIONS WITH PROTECTIVE CONTACT (SCHUKO)	0
APPLICATION	Data center/ facility/IT
OUTPUT EFFECTIVE POWER	15000 W
TRANSITION TIME FOR FULL LOAD	0 s
EFFICIENCY (IMPROVED EFFICIENCY MODE)	99 %
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	1 %
INTEGRATED FUNCTIONALITY	Network Mangement
COMMUNICATION INTERFACE	USB RS232
INPUT FREQUENCY - MIN	50 Hz
INPUT FREQUENCY - MAX	60 Hz
INPUT VOLTAGE - MIN	220 V
INPUT VOLTAGE - MAX	415 V
OUTPUT VOLTAGE - MIN	220 V
OUTPUT VOLTAGE - MAX	415 V

SECONDARY FREQUENCY MIN	50 Hz
SECONDARY FREQUENCY MAX	60 Hz
OUTPUT APPARENT POWER	15000 VA
PRIMARY FREQUENCY - MAX	60 Hz
PRIMARY FREQUENCY - MIN	50 Hz
RUNTIME AT HALF LOAD	16 min
RUNTIME AT FULL LOAD	3 min
MOUNTING METHOD	Tower Rackmount
NUMBER OF OUTPUT CONNECTIONS FRENCH STANDARD (TYPE E)	0
POWER CONSUMPTION	120
