



□□□□

Eaton 9PX8KIBP31

Eaton 9PX UPS 3:1 HotSwap, 8 kVA, 7.2 kW,
Input: Hardwired, Outputs: (4) C19,
Hardwired, Rack/tower, 6U

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX8KIBP31
UPC	743172040299
PRODUCT LENGTH/DEPTH	70 cm
PRODUCT HEIGHT	44 cm
PRODUCT WIDTH	26 cm
PRODUCT WEIGHT	88 kg
COMPLIANCES	CE Marked TUV
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 CE EAC



Powering Business Worldwide

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Energy efficient, reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (at the UPS level)
- Parallel operation using HotSync technology
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime

TOPOLOGY	Online/Double-conversion
RACK SIZE	6U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver
VA RATING	8 kVA
WATTAGE	7.2 kW
RACK MOUNTING KIT	No

PACKAGE CONTENTS

- Power Module
- Extended battery module (EBM)
- Maintenance Bypass
- USB cable
- Serial cable
- Battery cable with

- comms for automatic battery cabinet recognition
- (2) Supports for tower mounting
- Link plate
- Safety instructions
- Quickstart guide

INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	Hardwired/fixed connection
INPUT NOMINAL VOLTAGE	400V default (380/400/415V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(4) C19, Hardwired
NUMBER OF OUTPUTS C19	4
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	400V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240/250V)
FEED TYPE	2
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata

BATTERY MANAGEMENT

- ABM & Temperature compensated charging method (user selectable)
- Automatic battery test
- Deep discharge protection
- Automatic recognition of external battery units

BATTERY	Hot-swappable battery
----------------	-----------------------

REPLACEMENT	modules
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	16 min

COMMUNICATION	<ul style="list-style-type: none"> • USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Dry contacts (4 outputs, relay, DB9)
----------------------	--

EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 1472
NOISE LEVEL	<48 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	408 V
INPUT VOLTAGE - MIN	305 V
OUTPUT VOLTAGE - MAX	250 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	20
EFFICIENCY AT MAX. LOAD	95

EFFICIENCY (ECO-MODE)	98
INPUT VOLTAGE RANGE	305-480 V
MAX NUMBER OF BATTERY PACKS	12 (supercharger required for more than 6 EBM)
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	200/208/220/230/240/250 V +/- 1%
PHASE (INPUT)	3
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	5 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	2
POWER CONSUMPTION	432 W

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
 30 Pembroke Road
 Dublin 4, □□□□
 Eaton.com

