

Eaton 9701-2001-00P

Eaton DG1 Variable frequency drive, 230 V AC, 3-phase, 25 A, 5.5 kW, IP21/NEMA1, Brake chopper, DC link choke

PRODUCT NAME	Eaton DG1 variable frequency drive
CATALOG NUMBER	9701-2001-00P
PRODUCT LENGTH/DEPTH	244.7 mm
PRODUCT HEIGHT	419 mm
PRODUCT WIDTH	167.8 mm
PRODUCT WEIGHT	10.2 kg
CERTIFICATIONS	Safety requirements: IEC/EN 61800-5 CSA-C22.2 No. 274-13 UL Category Control No.: NMMS, NMMS7 UL CE UL report applies to both US and Canada IEC/EN 61800-3 Certified by UL for use in Canada RoHS, ISO 9001 C-Tick UkrSEPRO IEC/EN61800-3 Specification for general requirements: IEC/EN 61800-2 IEC/EN61800-5 CUL EAC UL508 UL File No.: E134360
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are

PRODUCT CATEGORY	Variable frequency drives
FEATURES	<p>Temperature-controlled fan Tool-less swapping of fan Parameterization: Fieldbus</p> <p>Parameterization: Keypad Parameterization: Power Xpert inControl</p>
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf
eaton-frequency-inverter-dg1-dimensions-002.eps
eaton-frequency-inverter-dg1-3d-drawing-002.eps

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Radio interference suppression filter DC link choke Multi-line graphic display Breaking resistance Brake chopper Additional PCB protection PC connection Control unit Internal DC link IGBT inverter
POLLUTION DEGREE	2
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	In conjunction with DXG-NET-SWD SmartWire DT module Yes
OPERATING MODE	U/f control

	Sensorless vector control (SLV) Torque regulation Speed control with slip compensation
FRAME SIZE	FS2
AIR VOLUME CAPACITY	94 m ³ /h
ALTITUDE	Max. 1000 m Max. 2000 m for Corner Grounded TN Systems Max. 3000 m Above 1000 m with 1 % derating per 100 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-30 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 230 V	12.3 kVA
APPARENT POWER AT 240 V	12.9 kVA
ASSIGNED MOTOR CURRENT IM AT 220 - 240 V, 60 HZ, 150% OVERLOAD	22 A
ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 110% OVERLOAD	26.4 A
ASSIGNED MOTOR	19.6 A

CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD	
ASSIGNED MOTOR CURRENT IM AT 230 V, 60 HZ, 110% OVERLOAD	28 A
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	100 kA
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
HEAT DISSIPATION DETAILS	Operation (with 150 % overload), allow for derating
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	16.62 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	425 VDC
VOLTAGE RATING - MAX	240 VAC
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	Modbus RTU, built in PROFIBUS, optional SmartWire-DT, optional Modbus TCP, built in CANopen®, optional DeviceNet, optional BACnet MS/TP, built in Ethernet IP, built in
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP21 NEMA 1
PROTOCOL	CAN TCP/IP BACnet Other bus systems MODBUS

	DeviceNet PROFIBUS PROFINET IO EtherNet/IP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	7.5 HP
SYSTEM CONFIGURATION TYPE	TN-S, TN-C, TN-C-S, TT, IT
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE, 110 % OVERLOAD	10 HP
BRAKING RESISTANCE	20 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	315 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 110% OVERLOAD	29 A
INPUT CURRENT ILN AT 150% OVERLOAD	23.1 A
MAINS CURRENT DISTORTION	33.3 %
CURRENT LIMITATION	0.1 - 2 x IH (CT), motor, main circuit
NUMBER OF SLOTS	2 (expansion)
BRAKING TORQUE	Adjustable to 150 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit Adjustable to 150 % (I/Ie), DC - Main circuit Max. 100 % of rated operational current Ie with external braking resistor - Main circuit
CABLE LENGTH	C2 \leq 10 m, Radio interference level, maximum motor cable length 150 m, screened, maximum permissible, Motor feeder

	C3 ≤ 50 m, Radio interference level, maximum motor cable length
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	230 V AC, 3-phase 240 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	8
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C1: with external filter, for conducted emissions only
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	315 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
EFFICIENCY	97.4 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA options incl.)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT	6 mA

GROUND IPE - MAX	
MAINS VOLTAGE - MAX	240 V
MAINS VOLTAGE - MIN	208 V
NOMINAL OUTPUT CURRENT I_{2N}	25 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	1
NUMBER OF HW-INTERFACES (OTHER)	1
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	5.5 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	7.5 kW
OUTPUT FREQUENCY - MAX	400 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	240 V
OVERLOAD CURRENT I_L AT 110% OVERLOAD	34.1 A
OVERLOAD CURRENT I_L AT 150% OVERLOAD	37.5 A
SHOCK RESISTANCE	Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 Storage and transportation: maximum 15 g, 11 ms (inside the packaging)

	UPS drop test (for weights inside the UPS frame)
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	4 kHz, 1 - 12 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	230 V AC, 3-phase 240 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	35 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
VIBRATION	Resistance: 15.8 – 150 Hz, 1 g, Maximum acceleration amplitude Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak) Resistance: 5 - 150 Hz, According to EN 61800-5-1, IEC/EN 60068-2-6
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	31 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	25 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	25 A
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 1-PHASE	5.5 kW
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE, 110% OVERLOAD	7.5 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL1, PLc Cat 1)
HEAT DISSIPATION AT CURRENT/SPEED	104 W at 25% current and 50% speed 125 W at 100% current and 50% speed 131 W at 100% current and 0% speed 148 W at 50% current and 50% speed 158 W at 50% current and 90% speed

267 W at 50% current and 0% speed 291 W at 100% current and 90% speed 86 W at 25% current and 0% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

