



## Eaton 9PX11KG2-L

Eaton 9PX Gen 2 UPS, Lithium-ion battery, 11000VA, 11000W, Input: Hardwired, Outputs: Hardwired, (4) L6-30R, 4U Rack/tower, Gigabit Network card included

□□□□

<b>PRODUCT NAME</b>	Eaton 9PX UPS
<b>CATALOG NUMBER</b>	9PX11KG2-L
<b>UPC</b>	786689972783
<b>PRODUCT LENGTH/DEPTH</b>	28.5 in
<b>PRODUCT HEIGHT</b>	6.85 in
<b>PRODUCT WIDTH</b>	17.32 in
<b>PRODUCT WEIGHT</b>	142.86 lb
<b>COMPLIANCES</b>	CISPR22 Class A / FCC part 15 Class A CE Marked FCC Part 15
<b>CERTIFICATIONS</b>	IEC 62040-2:2006 Cat C2 cULus Listed NOM ENERGY STAR certified



Powering Business Worldwide

<b>TOPOLOGY</b>	Online/Double-conversion
<b>RACK SIZE</b>	4U
<b>COLOR</b>	Black/silver
<b>VA RATING</b>	11 kVA
<b>WATTAGE</b>	11 kW
<b>RACK MOUNTING KIT</b>	Yes

<b>PACKAGE CONTENTS</b>	<ul style="list-style-type: none"> <li>• 11000VA 11000W 208V 9PX G2 Online Double- Conversion Lithium-Ion UPS</li> <li>• NETWORK-M3 Gigabit network card</li> <li>• USB cable</li> <li>• RS-232 cable</li> <li>• Cable gland for hardwire connection</li> <li>• Rack-mounting hardware</li> <li>• Tower support stands</li> <li>• Quick Start Guide</li> </ul>
-------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

<b>INTERNAL BYPASS</b>	Yes
<b>INPUT CONNECTION</b>	Hardwired
<b>INPUT NOMINAL VOLTAGE</b>	208V default (200/208/220/230/240V)
<b>INPUT FREQUENCY RANGE</b>	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
<b>INPUT POWER FACTOR</b>	>0.99 typical
<b>RECEPTACLE</b>	(4) L6-30R, Hardwired
<b>NUMBER OF OUTPUTS L6-30R</b>	4
<b>OUTPUT WAVEFORM</b>	True sine wave
<b>VOLTAGE</b>	208 V
<b>OUTPUT NOMINAL VOLTAGE</b>	208V default (200/208/220/230/240V)
<b>RUNTIME GRAPH</b>	\$row.attributeValue.cdata
<b>BATTERY MANAGEMENT</b>	On-board battery management system (BMS) monitors battery performance, lifecycle, and active temperature to provide advance notice when batteries need replacing
<b>BATTERY REPLACEMENT</b>	Hot-swappable internal

	batteries and extended battery modules (EBMs). Replacement battery part # EBP-1806-L (qty 2 per UPS).
<b>BATTERY TYPE</b>	Lithium-ion
<b>EXTENDED BATTERY CAPABILITY</b>	Add up to 10 EBMs, part # 9PXEBM192RTG2-L
<b>EXTENDED SERVICE PLANS</b>	<ul style="list-style-type: none"> <li>• 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC</li> <li>• - On-site parts and labor coverage for years 5</li> <li>• - Parts, electronics and UPS batteries coverage</li> <li>• - 24x7 on-site labor coverage, next-day response</li> <li>• - Next-day shipping</li> <li>• - Technical support</li> </ul>
<b>RUNTIME AT HALF LOAD</b>	16 min
<b>BATTERY CHEMISTRY</b>	Lithium Iron Phosphate (LiFePo4)
<b>EXPANSION SLOTS</b>	(2) Mini-Slot (MS) expansion ports with 1 Gigabit Network Card (NETWORK-M3) included
<b>ETHERNET INTERFACE</b>	Yes
<b>INCLUDES NETWORK CARD</b>	Yes
<b>SOFTWARE COMPATIBILITY</b>	Brightlayer Data Centers suite
<b>USER INTERFACE</b>	Graphical display, 5-button programmable menu, LED indicator
<b>ALTITUDE</b>	3000 m
<b>BTU RATING</b>	Online: 1160 BTU/hr, Battery: 1767 BTU/hr, High Efficiency: 188 BTU/hr
<b>NOISE LEVEL</b>	≤54 dB at 100% load, <38 dB at 66% load (at 1m, online mode, <87degrees F)
<b>RELATIVE HUMIDITY</b>	0-95% non-condensing
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>PROTOCOL</b>	SNMP
<b>PRODUCT HIGHLIGHTS</b>	Keeps equipment running during outages to allow time for file saves and safe

shutdown  
 Best-in-class efficiency results in reduced energy costs and greenhouse gas emissions  
 Included NETWORK-M3 Gigabit network card enables full remote access and control  
 Integrated battery management system (BMS) for temperature regulation and life cycle monitoring  
 Optional extended battery modules allow expanded runtime to keep equipment powered  
 Lithium-ion batteries have lifespan up to 10 years

<b>EFFICIENCY AT MAX. LOAD</b>	97%
<b>MAX NUMBER OF BATTERY PACKS</b>	10
<b>OUTPUT FREQUENCY</b>	50/60 Hz
<b>OUTPUT POWER FACTOR</b>	1.0
<b>OUTPUT VOLTAGE RANGE</b>	±1% steady-state
<b>RUNTIME AT FULL LOAD</b>	7.9 (11000W)
<b>INTERNAL BATTERY DETAILS</b>	192V 12Ah 2304Wh
<b>UPS POWER MODULE WEIGHT (LBS.)</b>	132.3

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House  
 30 Pembroke Road  
 Dublin 4, □□□  
 Eaton.com

