



□□□□

Eaton 9PX1500GRT-L

Eaton 9PX lithium ion UPS, 2U, 1500 VA, 1350 W at 208V, C14 input, Outputs: (8) C13, 208V

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX1500GRT-L
UPC	743172105400
PRODUCT LENGTH/DEPTH	17.72 in
PRODUCT HEIGHT	3.41 in
PRODUCT WIDTH	17.32 in
PRODUCT WEIGHT	34.83 lb
COMPLIANCES	FCC part 15 Class B IEC 62040-2 Cat C1
CERTIFICATIONS	NOM cTUVus ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide



TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
COLOR	Black/silver
VA RATING	1500 VA
WATTAGE	1350 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS	<ul style="list-style-type: none">• 1500VA 1350W 208V 9PX Online Double-Conversion UPS with 8 Outlets• USB cable• RS-232 cable• Rack-mounting hardware• Tower support stands• Safety guide• Quick Start Guide
-------------------------	---

INTERNAL BYPASS	Yes
INPUT CONNECTION	C14
INPUT CORD LENGTH	6 ft detachable
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
INPUT FREQUENCY RANGE	60 Hz: 50-70 Hz, 50 Hz: 40-60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	(8) C13, 208V
NUMBER OF OUTPUTS C13	8
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
RUNTIME GRAPH	<code>\$row.attributeValue.cdata</code>
BATTERY MANAGEMENT	Integrated battery management system (BMS) for temperature regulation and life cycle monitoring
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Lithium-ion
EXTENDED BATTERY CAPABILITY	Add up to 4 extended battery modules (EBM). Part number 9PXEBM48RT-L



STANDARD FACTORY WARRANTY	<ul style="list-style-type: none"> • 5-YEAR FACTORY WARRANTY • - 5 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
BATTERY CHEMISTRY	Lithium Iron Phosphate (LiFePo4)
COMMUNICATION	RS-232 (RJ45) ports; USB port as standard (HID). 6-foot RS-232 and USB cables included
EXPANSION SLOTS	<ul style="list-style-type: none"> • (1) Mini-Slot (MS) expansion port. The following optional connectivity cards may be ordered separately. • Gigabit Network Card part number: NETWORK-M3 • Modbus card part number: INDGW-M2 • Relay card part number: RELAY-MS
SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	Graphical display, 5-button programmable menu
ALTITUDE	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
BTU RATING	Online: 494, Battery: 731
NOISE LEVEL	<47 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PRODUCT HIGHLIGHTS	<p>Keeps equipment running during outages to allow time for file saves and safe shutdown</p> <p>Improved lithium-ion batteries have service life up to 10 years - set it and forget it!</p> <p>Provides 80% to 120% more runtime at full load than equivalent lead-acid UPS systems</p> <p>Interactive LCD interface keeps you updated on</p>

