



□□□□□

Eaton 9PX1500IRT2UBS

Eaton 9PX UPS, 1500 VA, 1500 W, Input: C14, Outputs: (8) C13, Rack/tower, 2U, with BS input cord

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX1500IRT2UBS
PRODUCT LENGTH/DEPTH	450 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	440 mm
PRODUCT WEIGHT	19.7 kg
COMPLIANCES	CISPR22 Class B CE Marked TUV cULus Listed CSA 22.2 FCC part 15 Class B
CERTIFICATIONS	UL 1778 EAC CE ENERGY STAR certified IEC/EN 62040-1 IEC/EN 62040-2

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- First UPS in its class to provide Unity power factor (VA=W)
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (down to the managed outlet groups)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	1500 VA
WATTAGE	1500 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	• UPS

- (2) IEC-IEC output cables
- USB cable
- Serial cable
- (2) brackets for 19" mounting
- (2) Rack-mounting kit
- (2) Supports for tower mounting
- Cable locking system
- Safety instructions
- Quickstart guide
- BS input cord

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13
NUMBER OF OUTPUTS C13	8
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph
BATTERY MANAGEMENT	• ABM & Temperature compensated charging method (user selectable) • Automatic battery test • Deep discharge protection

	Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	14 min
COMMUNICATION	- USB port (HID compliant) - Serial port (RS232) - Mini terminal block for remote On/Off - Mini-terminal block for remote power off - Mini-terminal block for output relay - Dry contacts (3 outputs, 1 input, optocoupler, DB9)
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 386
NOISE LEVEL	<35 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	100 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V

SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	4
EFFICIENCY AT MAX. LOAD	92.5
EFFICIENCY (ECO-MODE)	97.5
INPUT VOLTAGE RANGE	176-276 V (100-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 1%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	5 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3

□□□□:
□□□□:
□□□:
□□: