


Eaton 9SX1000

Eaton 9SX online, extended runtime UPS, 1000 VA, 900 W, 5-15P input, Outputs: (6) 5-15R, 9.9"Hx6.3"Wx15.1"D, 30.9 lb., network card optional

PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX1000
UPC	743172091239
PRODUCT LENGTH/DEPTH	15.1 in
PRODUCT HEIGHT	9.9 in
PRODUCT WIDTH	6.3 in
PRODUCT WEIGHT	30.9 lb
COMPLIANCES	FCC Compliant CE Marked ENERGY STAR certified
CERTIFICATIONS	cULus Listed ICC-ES AC156 OSHPD Seismic certified

SPECIAL FEATURES	This product is designed with features typically required in commercial applications, including network connectivity and a metal case
TOPOLOGY	Online/Double-conversion
RACK SIZE	0U
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	1000 VA
WATTAGE	900 W
PACKAGE CONTENTS	• 9SX1000 Eaton 9SX Double-Conversion UPS • USB cable • RS-232 cable • Quick start guide
INTERNAL BYPASS	Yes
INPUT CONNECTION	5-15P
INPUT CORD LENGTH	8 ft
INPUT NOMINAL VOLTAGE	120 Default (100/110/120/125V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(6) 5-15R
NUMBER OF OUTPUTS 5-15R	6
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120V
OUTPUT NOMINAL VOLTAGE	120V default (100/110/120/125V)
FEED TYPE	1
RUNTIME GRAPH	View runtime graph
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
EXTENDED BATTERY CAPABILITY	Yes
STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support



EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • -5-year depot repair: 9SW5Y-1000UC • -Expedited parts coverage for 5 years • -Parts, electronics and UPS batteries coverage • -Next business day shipping • -Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-2509UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support
COMMUNICATION	• (1) MiniSlot • (1) USB port • (1) Serial RS-232 port • (1) RPO/ROO/Signal input terminal • (1) mini-terminal block for output relay
EXPANSION SLOTS	• (1) Mini-Slot (MS) expansion port. Optional connectivity cards may be ordered separately. • - Gigabit Web/SNMP card part number: NETWORK-M3 • - Modbus card part number: INDGW-M2 • - Relay card part number: RELAY-MS
USER INTERFACE	5-button graphical user interface
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online : 421 BTU/hr, Battery : 505 BTU/hr, High efficiency : 208 BTU/hr
NOISE LEVEL	51 dB at 1m
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
MOUNTING METHOD	Vertical
EFFICIENCY AT MAX. LOAD	90.81

MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9

:
:
:
:

