

Eaton 9SX1000IR

Eaton 9SX UPS, 1000 VA, 900 W, Input: C14,
Outputs: (6) C13, Rack, 2U

PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX1000IR
UPC	743172090959
PRODUCT LENGTH/DEPTH	438 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	438 mm
PRODUCT WEIGHT	15.7 kg
COMPLIANCES	CE Marked TUV cULus Listed CSA 22.2 FCC part 15 Class B CISPR22 Class B
CERTIFICATIONS	IEC/EN 62040-1 UL 1778 IEC/EN 62040-2 CE cULus Listed EAC

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Energy efficient, reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Meter energy consumption (at the UPS level)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime
- Long backup time with up to 4 optional EBM
- Cable locking system

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Rack
RACK SIZE	2U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black
VA RATING	1000 VA
WATTAGE	900 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none">• UPS• (2) IEC-IEC output cables• USB cable• Serial cable

	<ul style="list-style-type: none">• (2) brackets for 19' mounting• (2) Rack-mounting kit• Safety instructions• Quickstart guide
INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240/250V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(6) C13
NUMBER OF OUTPUTS C13	6
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	<ul style="list-style-type: none">• ABM & Temperature compensated charging method (user selectable)• Automatic battery test• Deep discharge protection• Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)

BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	16.5 min

COMMUNICATION	<ul style="list-style-type: none"> • USB port (HID compliant) • Serial port (RS232) • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (2 outputs, 1 input, optocoupler, DB9)
----------------------	--

EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 375
NOISE LEVEL	<41 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	120 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	3

EFFICIENCY AT MAX. LOAD	89
EFFICIENCY (ECO-MODE)	95
INPUT VOLTAGE RANGE	190-276 Vac without derating (up to 120-276 Vac with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 2%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	6 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
POWER CONSUMPTION	110 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

