

## Eaton 9SX3000INB

Eaton 9SX UPS without battery, 3000 VA,  
2700 W, Input: C20, Outputs: (8) C13, (1) C19,  
Tower

|                      |               |
|----------------------|---------------|
|                      |               |
| PRODUCT NAME         | Eaton 9SX UPS |
| CATALOG NUMBER       | 9SX3000INB    |
| UPC                  | 743172091031  |
| PRODUCT LENGTH/DEPTH | 412 mm        |
| PRODUCT HEIGHT       | 346 mm        |
| PRODUCT WIDTH        | 214 mm        |
| PRODUCT WEIGHT       | 19.3 kg       |

|                        |                                                                                                                                                                     |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                        |                                                                                                                                                                     |
| TOPOLOGY               | Online/Double-conversion                                                                                                                                            |
| FORM FACTOR            | Tower                                                                                                                                                               |
| CONSTRUCTION TYPE      | Free standing model                                                                                                                                                 |
| COLOR                  | Black                                                                                                                                                               |
| VA RATING              | 3000 VA                                                                                                                                                             |
| WATTAGE                | 2700 W                                                                                                                                                              |
| PACKAGE CONTENTS       | 9SX 3000VA UPS, Quick Start Guide, (2) IEC C13-C14 jumpers 1.8m, serial cable, usb cable                                                                            |
| INTERNAL BYPASS        | Yes                                                                                                                                                                 |
| HOT SWAP POWER         | No                                                                                                                                                                  |
| AUTO SHUTDOWN FUNCTION | Yes                                                                                                                                                                 |
| TYPE OF ACCESSORY      | Other                                                                                                                                                               |
| INPUT CONNECTION       | C20                                                                                                                                                                 |
| INPUT CORD LENGTH      | 1.8m                                                                                                                                                                |
| INPUT NOMINAL VOLTAGE  | 230V default<br>(200/208/220/230/240V)                                                                                                                              |
| NOMINAL FREQUENCY      | 50/60 Hz                                                                                                                                                            |
| INPUT FREQUENCY RANGE  | 40-70 Hz                                                                                                                                                            |
| INPUT POWER FACTOR     | >.99                                                                                                                                                                |
| RECEPTACLE             | (8) C13, (1) C19                                                                                                                                                    |
| NUMBER OF OUTPUTS C13  | 8                                                                                                                                                                   |
| NUMBER OF OUTPUTS C19  | 1                                                                                                                                                                   |
| OUTPUT WAVEFORM        | Sine wave                                                                                                                                                           |
| VOLTAGE                | 230V                                                                                                                                                                |
| OUTPUT NOMINAL VOLTAGE | 230V default<br>(200/208/220/230/240V)                                                                                                                              |
| FEED TYPE              | 1                                                                                                                                                                   |
| RUNTIME GRAPH          | View runtime graph                                                                                                                                                  |
| BATTERY MANAGEMENT     | ABM & Temperature compensated charging method (user selectable), Automatic battery test, deep discharge protection, automatic recognition of external battery units |
| BATTERY REPLACEMENT    | Hot-swappable internal batteries and extended battery modules (EBMs)                                                                                                |



|                                                      |                                                                                                                                           |
|------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| <b>BATTERY TYPE</b>                                  | Sealed, lead-acid                                                                                                                         |
| <b>EXTENDED BATTERY CAPABILITY</b>                   | Yes                                                                                                                                       |
| <b>COMMUNICATION</b>                                 | 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay Communication slot |
| <b>EXPANSION SLOTS</b>                               | One slot for optional communication card                                                                                                  |
| <b>ETHERNET INTERFACE</b>                            | No                                                                                                                                        |
| <b>INCLUDES NETWORK CARD</b>                         | No                                                                                                                                        |
| <b>SOFTWARE COMPATIBILITY</b>                        | Eaton Intelligent Power Manager, Eaton Intelligent Power Protector                                                                        |
| <b>USER INTERFACE</b>                                | Multilingual graphical LCD display                                                                                                        |
| <b>POTENTIAL FREE SWITCH CONTACT</b>                 | Yes                                                                                                                                       |
| <b>ALTITUDE</b>                                      | 3000 m                                                                                                                                    |
| <b>BTU RATING</b>                                    | Online: 818                                                                                                                               |
| <b>NOISE LEVEL</b>                                   | <45 dB at 1 meter                                                                                                                         |
| <b>RELATIVE HUMIDITY</b>                             | 0-96% non-condensing                                                                                                                      |
| <b>TEMPERATURE RANGE</b>                             | 0° to 40°C (32° to 104°F)                                                                                                                 |
| <b>BATTERY QUANTITY</b>                              | 0                                                                                                                                         |
| <b>EFFICIENCY AT MAX. LOAD</b>                       | 92.4                                                                                                                                      |
| <b>EFFICIENCY (ECO-MODE)</b>                         | 97.4                                                                                                                                      |
| <b>INPUT VOLTAGE RANGE</b>                           | 200-276 V (140 V-276 V with derating)                                                                                                     |
| <b>MAX NUMBER OF BATTERY PACKS</b>                   | 4                                                                                                                                         |
| <b>OUTPUT FREQUENCY</b>                              | 50/60 Hz                                                                                                                                  |
| <b>OUTPUT POWER FACTOR</b>                           | 0.9                                                                                                                                       |
| <b>OUTPUT VOLTAGE RANGE</b>                          | 200/208/220/230/240 V +/- 2%                                                                                                              |
| <b>PHASE (INPUT)</b>                                 | 1                                                                                                                                         |
| <b>PHASE (OUTPUT)</b>                                | 1                                                                                                                                         |
| <b>VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX</b> | 3                                                                                                                                         |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

