



□□□□□

Eaton 9PX2200IRTNBS

Eaton 9PX UPS Netpack, 2200 VA, 2200 W,
Input: C20, Outputs: (8) C13, (2) C19,
Rack/tower, 2U, Network card included, with
BS input cord

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX2200IRTNBS
PRODUCT LENGTH/DEPTH	605 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	440 mm
PRODUCT WEIGHT	28.3 kg
COMPLIANCES	CE Marked TUV cULus Listed CSA 22.2 FCC part 15 Class B CISPR22 Class B
CERTIFICATIONS	IEC/EN 62040-1 UL 1778 IEC/EN 62040-2 EAC CE ENERGY STAR certified

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- First UPS in its class to provide Unity power factor (VA=W)
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Network card and rackmounting kit delivered as standard
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (down to the managed outlet groups)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime

TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	2200 VA
WATTAGE	2200 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS

- UPS
- Input cable
- (2) IEC-IEC output cables
- Network Management Card
- USB cable
- Serial cable
- (2) Supports for tower mounting
- (2) brackets for 19" mounting
- (2) Rack-mounting kit
- Cable locking system
- Safety instructions
- Quickstart guide
- BS input cord

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C20
INPUT CORD LENGTH	1.8m
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13, (2) C19
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	2
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph

BATTERY MANAGEMENT

- ABM & Temperature compensated
-

	charging method (user selectable) • Automatic battery test • Deep discharge protection • Automatic recognition of external battery units
--	---

BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY RATING	12 V / 7 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	10 min

COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (3 outputs, 1 input, optocoupler, DB9) • Network Card
---------------	---

EXPANSION SLOTS	One slot, network card included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 488
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing

TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PROTOCOL	SNMP
INTEGRATED FUNCTIONALITY	Network Mangement
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	100 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	6
EFFICIENCY AT MAX. LOAD	93.5
EFFICIENCY (ECO-MODE)	98
INPUT VOLTAGE RANGE	176-276 V (100-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 1%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	3 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)

□□□□:
□□□□:
□□□:
□□: