



Eaton 9PXM08AAXXX

Eaton 9PXM UPS frame, 4-16 kVA, Hardwired input, Hardwired output, Rack/Tower, 14U

□□□□

PRODUCT NAME	Eaton 9PXM UPS
CATALOG NUMBER	9PXM08AAXXX
UPC	743172091406
PRODUCT LENGTH/DEPTH	34.5 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	125 lb
COMPLIANCES	TAA Compliant FCC Compliant
CERTIFICATIONS	IEC Rated cULus Listed

TOPOLOGY	Online/Double-conversion
RACK SIZE	14U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver
PACKAGE CONTENTS	• 9PXM08AAXXX 9PXM 208/240V Online Double- Conversion UPS Cabinet • Owner's manual
INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	Hardwired
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120/208V
OUTPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
FEED TYPE	1
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
STANDARD FACTORY WARRANTY	• 2-YEAR FACTORY WARRANTY • - 2 years • Parts, labor, electronics and

batteries coverage*

- - Startup included
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support
- *if startup is performed by Eaton, if self-performed startup then just 90 days labor

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-11000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

EXPANSION SLOTS

- (2) Mini-Slot (MS) expansion ports. The following optional connectivity cards may be ordered separately.
- Gigabit Network Card part number: NETWORK-M2
- Modbus card part number: INDGW-

M2 Relay card part number: RELAY-MS	
SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	5-Button Graphical User Interface
RELATIVE HUMIDITY	5-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
MAX NUMBER OF BATTERY PACKS	8
OUTPUT FREQUENCY	60 Hz
OUTPUT POWER FACTOR	0.9
