

Eaton AAO32

Eaton Bussmann series low voltage british standard fuse, 32A, AC 550 V, V88/A2, 14 x 85 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AAO32
UPC	051712838436
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	20.1 g
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	32 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A2
CURRENT TYPE	AC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
CLASS	Class gG/gL
FUSE TYPE	AAO
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.1 W
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A2
CONSTRUCTION SIZE	A2
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	CM32F Camaster fuse holder RS32 Red spot fuse holder
QUANTITY	20
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250978en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

