



## Eaton AAO32M35

Eaton Bussmann series low voltage british standard fuse, 32A, AC 500 V, V88/A2, 22 x 85 mm, gM, 32M35

□□□□

|                                 |   |
|---------------------------------|---|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>low voltage british<br>standard fuse |
| <b>CATALOG NUMBER</b>           | AAO32M35  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 85 mm   |
| <b>PRODUCT HEIGHT</b>           | 21 mm   |
| <b>PRODUCT WIDTH</b>            | 21 mm   |
| <b>PRODUCT WEIGHT</b>           | 50.1 g  |
| <b>COMPLIANCES</b>              | CE Marked<br>RoHS Compliant                                   |
| <b>CERTIFICATIONS</b>           | BS88<br>IEC 60269<br>EAC                                      |



Powering Business Worldwide

□□□□

|   |  |
|---|--|
| <b>AMPERAGE RATING</b>                                  | 35 A   |
| <b>FITTED WITH:</b>                                     | Offset bolted tags   |
| <b>FUSE SIZE</b>  | BS88/A2  |
| <b>CURRENT TYPE</b>                                     | AC   |
| <b>MOUNTING DIMENSION</b>                               | M5   |
| <b>CENTER-TO-CENTER<br/>DISTANCE OF<br/>CONNECTIONS</b> | 73 mm  |
| <b>BREAKING CAPACITY</b>                                | 80 kA  |
| <b>RATED SWITCHING<br/>CAPACITY</b>                     | 80 kA  |
| <b>MOTOR CURRENT<br/>RATING</b>                         | 32M35  |
| <b>RATED VOLTAGE AC</b>                                 | 500 V  |
| <b>CLASS</b>  | Class gM   |
| <b>FUSE TYPE</b>  | AAO  |
| <b>UTILIZATION CATEGORY</b>                             | gM (motor protection)                                      |
| <b>COLOR</b>  | None   |
| <b>INTERRUPT RATING</b>                                 | 80 kAIC  |
| <b>FUSE INDICATOR</b>                                   | None   |
| <b>INSULATED METAL<br/>GRIPPING LUGS (IMGL)</b>         | No   |
| <b>CONNECTION</b>                                       | 73 mm fixing centre  |
| <b>CONSTRUCTION</b>                                     | BS88/A2  |
| <b>CONSTRUCTION SIZE</b>                                | A2   |
| <b>FUSE SHAPE</b>                                       | Offset bolted tags   |
| <b>VOLTAGE TYPE</b>                                     | AC   |
| <b>SUITABLE FOR</b>                                     | CM32F Camaster fuse<br>holder<br>RS32 Red spot fuse holder |
| <b>VOLTAGE RATING</b>                                   | 500 V  |
| <b>TYPE</b>   | Fuse   |
| <b>APPLICATION</b>                                      | general industrial<br>applications                         |
| <b>FUSE SYSTEM<br/>(ACCORDING TO IEC<br/>60269)</b>     | Fuse system E  |

□□

DECLARATIONS OF  
CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250939en.pdf](#)

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

