

Eaton AAO32M63

Eaton Bussmann series low voltage british standard fuse, 32A, AC 500 V, V88/A2, 22 x 85 mm, gM, 32M63

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AAO32M63
UPC	051712838467
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	50.1 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 BS88

AMPERAGE RATING	63 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A2
CURRENT TYPE	AC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	32M63
RATED VOLTAGE AC	500 V
CLASS	Class gM
FUSE TYPE	AAO
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A2
CONSTRUCTION SIZE	A2
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	CM32F Camaster fuse holder RS32 Red spot fuse holder
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250939en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

