



□□□□

Eaton ADE4M162NPN

Eaton Crouse-Hinds series Capri ADE-4F cable gland, 2 (M), Straight, Gland size 5, Armoured, Nickel plated brass, 7-12 outer sheath, Flameproof and increased safety, Silicone seal, M16 Metric

□□□□

PRODUCT NAME	Eaton's Crouse-Hinds series Capri ADE-4F cable gland
CATALOG NUMBER	ADE4M162NPN
PRODUCT LENGTH/DEPTH	57 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	19 mm
PRODUCT WEIGHT	53 g



Powering Business Worldwide

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX IEC NEC/CEC
NEC HAZARDOUS RATING	Class I, Zone 2
IECEX/ATEX HAZARDOUS RATING	Zone 22 Zone 2 Zone 21 Zone 1
INGRESS PROTECTION (IP) RATINGS	IP68 IP66
MATERIAL	Nickel plated brass
CABLE SEALING RANGE	2 (M)
CONNECTOR TYPE	Straight
GLAND SIZE	5
GLAND TYPE	Armoured
OUTER SHEATH (MIN/MAX)	7-12
PROTECTION TYPE	Flameproof and increased safety
SEALING TYPE	Silicone
THREAD SIZE	M16
NOMINAL THREAD SIZE METRIC/PG	16
PITCH THREAD	1.5 mm
THREAD LENGTH	15 mm
WRENCH WIDTH	19 mm
HEXAGON ANGULAR DIMENSION	20.9 mm
SUITABLE FOR CABLE DIAMETER - MAX	12 mm
SUITABLE FOR CABLE DIAMETER - MIN	7 mm
MATERIAL QUALITY	Brass
SURFACE PROTECTION	Nickel-plated
DEGREE OF PROTECTION (IP)	IP68
MODEL	Straight
TYPE OF SEALING	Sealing ring
WORKING TEMPERATURE - MAX	140 °C
WORKING TEMPERATURE - MIN	-60 °C
FOR EX-ZONE GAS	1, 2

