



□□□□

Eaton ADE4M203SSN

Eaton Crouse-Hinds series Capri ADE-4F cable gland, 3 (L), Straight, Gland size 7, Armoured, Stainless steel, 13.5-21 outer sheath, Flameproof and increased safety, Silicone seal, M20 Metric

□□□□

PRODUCT NAME	Eaton's Crouse-Hinds series Capri ADE-4F cable gland
CATALOG NUMBER	ADE4M203SSN
PRODUCT LENGTH/DEPTH	70 mm
PRODUCT HEIGHT	33 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	121 g



Powering Business Worldwide

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX IEC NEC/CEC
NEC HAZARDOUS RATING	Class I, Zone 2
IECEX/ATEX HAZARDOUS RATING	Zone 1 Zone 2 Zone 21 Zone 22
INGRESS PROTECTION (IP) RATINGS	IP68 IP66
MATERIAL	Stainless steel
CABLE SEALING RANGE	3 (L)
CONNECTOR TYPE	Straight
GLAND SIZE	7
GLAND TYPE	Armoured
OUTER SHEATH (MIN/MAX)	13.5-21
PROTECTION TYPE	Flameproof and increased safety
SEALING TYPE	Silicone
THREAD SIZE	M20
NOMINAL THREAD SIZE METRIC/PG	20
PITCH THREAD	1.5 mm
THREAD LENGTH	15 mm
WRENCH WIDTH	30 mm
HEXAGON ANGULAR DIMENSION	33 mm
SUITABLE FOR CABLE DIAMETER - MAX	21 mm
SUITABLE FOR CABLE DIAMETER - MIN	13.5 mm
MATERIAL QUALITY	Stainless steel V4A
SURFACE PROTECTION	Untreated
DEGREE OF PROTECTION (IP)	IP68
MODEL	Straight
TYPE OF SEALING	Sealing ring
WORKING TEMPERATURE - MAX	140 °C
WORKING TEMPERATURE - MIN	-60 °C
FOR EX-ZONE GAS	1, 2

