



□□□□□

Eaton 9SX3000IMBS

Eaton 9SX Marine UPS, 3000 VA, 2700 W,
Input: C20, Outputs: (8) C13, (1) C19, Tower,
with BS input cord

□□□□

PRODUCT NAME	Eaton 9SX Marine UPS
CATALOG NUMBER	9SX3000IMBS
PRODUCT LENGTH/DEPTH	41.2 mm
PRODUCT HEIGHT	34.6 mm
PRODUCT WIDTH	21.4 mm
PRODUCT WEIGHT	34 kg
COMPLIANCES	CE Marked TUV cULus Listed CSA 22.2 FCC part 15 Class B CISPR22 Class B
CERTIFICATIONS	IEC/EN 62040-1 UL 1778 IEC/EN 62040-2 CE EAC DNV GL Certified

SPECIAL FEATURES

- DNV-GL approved
- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Energy efficient, reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Meter energy consumption (at the UPS level)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	3000 VA
WATTAGE	2700 W
RACK MOUNTING KIT	No
PACKAGE CONTENTS	• UPS • Quickstart guide • (2) IEC-IEC output cables • Serial cable • USB cable • BS input cord
INTERNAL BYPASS	Yes
HOT SWAP POWER	No

AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C20
INPUT CORD LENGTH	1.8m
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13, (1) C19
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph
BATTERY MANAGEMENT	• ABM & Temperature compensated charging method (user selectable) • Automatic battery test • Deep discharge protection • Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	15.5 min
COMMUNICATION	• USB port (HID compliant)

	• Serial port (RS232) • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (2 outputs, 1 input, optocoupler, DB9)
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 818
NOISE LEVEL	<45 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	140 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	8
EFFICIENCY AT MAX. LOAD	92.4
EFFICIENCY (ECO-MODE)	97.4
INPUT VOLTAGE RANGE	200-276 V (140 V-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 2%
PHASE (INPUT)	1

PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	6 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

