



□□□□

Eaton 9SX700IBS

Eaton 9SX UPS, 700 VA, 630 W, Input: C14,
Outputs: (6) C13, Tower, with BS input cord

□□□□

PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX700IBS
PRODUCT LENGTH/DEPTH	357 mm
PRODUCT HEIGHT	252 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	11.5 kg
CERTIFICATIONS	IEC/EN 62040-1 UL 1778 IEC/EN 62040-2 CE cULus Listed EAC



Powering Business Worldwide

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Meter energy consumption (at the UPS level)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	700 VA
WATTAGE	630 W
RACK MOUNTING KIT	No
PACKAGE CONTENTS	<ul style="list-style-type: none"> • UPS • (2) IEC-IEC output cables • USB cable • Serial cable • Safety instructions • Quickstart guide • BS input cord
INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes

PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(6) C13
NUMBER OF OUTPUTS C13	6
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph

- BATTERY MANAGEMENT**
- ABM & Temperature compensated charging method (user selectable)
 - Automatic battery test
 - Deep discharge protection
 - Automatic recognition of external battery units

BATTERY REPLACEMENT	Hot-swappable internal batteries
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	13.5 min

- COMMUNICATION**
- USB port (HID compliant)
 - Serial port (RS232)
 - Mini-terminal block for remote power off
 - Mini-terminal block

- for output relay
- Dry contacts (2 outputs, 1 input, optocoupler, DB9)

EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 310
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	120 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	2
EFFICIENCY AT MAX. LOAD	87.4
EFFICIENCY (ECO-MODE)	93
INPUT VOLTAGE RANGE	190-276 V (120 V-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 2%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	5 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3

