




Eaton B127A-010-H

Signal Repeater for B127A Extenders, Over Cat6, 4K 60Hz, HDR, 4:4:4, PoC, HDCP 2.2, 400 ft., TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series extender
CATALOG NUMBER	B127A-010-H
UPC	037332261342
PRODUCT LENGTH/DEPTH	2.36 in
PRODUCT HEIGHT	0.59 in
PRODUCT WIDTH	1.02 in
PRODUCT WEIGHT	0.17 lb
WARRANTY	1 year limited
COMPLIANCES	REACH FCC Compliant CE Marked RoHS

□□□□	
TYPE	Signal Booster
RELATIVE HUMIDITY	0-85% non-condensing
COLOR	Black
MATERIAL	Plastic (PC)
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	HDR Support Consumer Electronics Control (CEC) Supported Daisy-chainable / Cascadable Power Over Cable (PoC) Support TAA Compliant 3D Video Supported EDID Compatible IR Remote Extension Support
COLOR DEPTH	36-bit Deep color 36-bit Deep Color
PACKAGE CONTENTS	Owner's manual B127A-010-H HDMI Repeater
PRODUCT HIGHLIGHTS	Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy Compatible with all B127A-Series HDMI, DisplayPort and USB-C models Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video 1-year limited warranty (Worldwide) Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases Power over Cable (PoC) technology provides power to the repeater via Cat6 cable
PACKAGING TYPE	Box
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR3	RJ45 (FEMALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	HDMI



	Cat6
FEATURES	Flex Center
CONNECTOR GROUP	RJ45
CONNECTOR	RJ45 (female)
MAXIMUM SIGNAL RANGE	201+ Foot
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 @ 60 Hz (4K x 2K)
RECOMMENDED CATEGORY CABLE	Cat6
MAX. DISTANCE (BETWEEN ANY 2 UNITS)	Transmitter and Receiver (1 to 1) = 400 ft.
TRANSMISSION DISTANCE	400 ft. (120 m)
LED INDICATORS	Green = Power
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
VIDEO INPUT	HDMI (FEMALE)
VIDEO OUTPUT	HDMI (FEMALE)
MAX RESOLUTION	4K/60
EXTENDER STYLE	Box
EXTENSION METHOD	CATx
TAA COMPLIANCE	Yes

□□□□:
□□□□:
□□□:
□□: