



Eaton AAO32M40

Eaton Bussmann series low voltage british standard fuse, 32A, AC 500 V, V88/A2, 22 x 85 mm, gM, BS88/A2, 32M40

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AAO32M40
UPC	051712838443
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	47.3 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 BS88



Powering Business Worldwide

□□□□

AMPERAGE RATING	40 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A2
CURRENT TYPE	AC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	32M40
RATED VOLTAGE AC	500 V
CLASS	Class gM
FUSE TYPE	AAO
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A2
CONSTRUCTION SIZE	A2
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	CM32F Camaster fuse holder RS32 Red spot fuse holder
QUANTITY	20
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250939en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

