

Eaton AD32

Eaton Bussmann series low voltage British standard fuse, 32 A, 500 V, 80 kAIC, 3.5 Watt, 111 mm fixing centre

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AD32
UPC	051712844826
PRODUCT LENGTH/DEPTH	129 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	62.9 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

AMPERAGE RATING	32 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	AD
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.5 W
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC AC/DC
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250945en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

