



□□□□

Eaton ADE4M163NPN

Eaton Crouse-Hinds series Capri ADE-4F cable gland, 3 (L), Straight, Gland size 6, Armoured, Nickel plated brass, 10-16 outer sheath, Flameproof and increased safety, Silicone seal, M16 Metric

□□□□

PRODUCT NAME	Eaton's Crouse-Hinds series Capri ADE-4F cable gland
CATALOG NUMBER	ADE4M163NPN
PRODUCT LENGTH/DEPTH	63 mm
PRODUCT HEIGHT	26.4 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	80 g



Powering Business Worldwide

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IEC IECEX/ATEX NEC/CEC
NEC HAZARDOUS RATING	Class I, Zone 2
IECEX/ATEX HAZARDOUS RATING	Zone 1 Zone 22 Zone 2 Zone 21
INGRESS PROTECTION (IP) RATINGS	IP66 IP68
MATERIAL	Nickel plated brass
CABLE SEALING RANGE	3 (L)
CONNECTOR TYPE	Straight
GLAND SIZE	6
GLAND TYPE	Armoured
OUTER SHEATH (MIN/MAX)	10-16
PROTECTION TYPE	Flameproof and increased safety
SEALING TYPE	Silicone
THREAD SIZE	M16
NOMINAL THREAD SIZE METRIC/PG	16
PITCH THREAD	1.5 mm
THREAD LENGTH	15 mm
WRENCH WIDTH	24 mm
HEXAGON ANGULAR DIMENSION	26.4 mm
SUITABLE FOR CABLE DIAMETER - MAX	16 mm
SUITABLE FOR CABLE DIAMETER - MIN	10 mm
MATERIAL QUALITY	Brass
SURFACE PROTECTION	Nickel-plated
DEGREE OF PROTECTION (IP)	IP68
MODEL	Straight
TYPE OF SEALING	Sealing ring
WORKING TEMPERATURE - MAX	140 °C
WORKING TEMPERATURE - MIN	-60 °C
FOR EX-ZONE GAS	1, 2

