



## Eaton BD63

Eaton Bussmann series low voltage british standard fuse, 63 A, 500 Vac, 21 x 129 mm, gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	BD63
<b>UPC</b>	051712838603
<b>PRODUCT LENGTH/DEPTH</b>	129 mm
<b>PRODUCT HEIGHT</b>	21 mm
<b>PRODUCT WIDTH</b>	21 mm
<b>PRODUCT WEIGHT</b>	66.9 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-2 BS88

□□□□

AMPERAGE RATING	63 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	BD
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	5.6 W
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC AC/DC
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF  
CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250945en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

