



Eaton B114-004-R

4-Port VGA/SVGA Video Splitter with Signal Booster, High Resolution Video, 350MHz, (HD15 M/4xF)

□□□□

PRODUCT NAME	Eaton Tripp Lite series splitter
CATALOG NUMBER	B114-004-R
UPC	037332014276
PRODUCT LENGTH/DEPTH	9.9 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	5.7 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS REACH FCC Compliant CE Marked

TYPE	Splitter
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	0-80% non-condensing
COLOR	Black
MATERIAL	Steel
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible Cascadable Daisy-chainable / Cascadable
PACKAGE CONTENTS	External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.3A; Output: 9V, 1A) B114-004-R VGA/SVGA Video Splitter - 4 Port Owner's manual
PRODUCT HIGHLIGHTS	Simultaneously displays video on up to 4 VGA/SVGA monitors A built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210-ft. (64 m) from the source 350Mhz bandwidth support 3-year limited warranty (Worldwide) The splitter can be located up to 25-ft. (7.62 m) from the connected computer, and up to 185-ft. (56.38 m) from the connected monitors
PACKAGING TYPE	Box
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.1 x 12 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	HD15 (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC

	208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	HD15 (MALE)
TECHNOLOGY	VGA / SVGA VGA/SVGA
FEATURES	Flex Center
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male) HD15 (female)
AC POWER ADAPTER CORD LENGTH	5 ft
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.3A; Output: 9V, 1A, 5 ft.
BTUS	6.1 BTU/Hr
DAISY-CHAINABLE OR CASCADABLE	Cascadable
MAX SUPPORTED VIDEO RESOLUTION	2048 x 1536 @ 60Hz
MAX. DISTANCE (BETWEEN ANY 2 UNITS)	246 ft. (75m)
LED INDICATORS	Green (Power)
OPERATING TEMPERATURE RANGE	32° to 122°F (0° to 50°C)
STORAGE TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
NUMBER OF PORTS	4
POWER CONSUMPTION	1.8 W
MAX RESOLUTION	1536p
INPUT X OUTPUT	1 x 4

□□□□:
□□□□:
□□□:
□□: