



□□□□

## Eaton CAP169114

Eaton Crouse-Hinds series Capri NEWCAP CT cable gland, 6-13 cable range, Gland size 6, Non-armoured, Nickel plated brass, Industrial, PG 11

□□□□

<b>PRODUCT NAME</b>	Eaton's Crouse-Hinds series Capri NEWCAP CT cable gland
<b>CATALOG NUMBER</b>	CAP169114
<b>PRODUCT LENGTH/DEPTH</b>	35 mm
<b>PRODUCT HEIGHT</b>	24 mm
<b>PRODUCT WIDTH</b>	26 mm
<b>PRODUCT WEIGHT</b>	37.5 g



Powering Business Worldwide

□□□□

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	IEC
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66 IP68
<b>MATERIAL</b>	Nickel plated brass
<b>CABLE RANGE (MIN/MAX)</b>	6-13
<b>GLAND SIZE</b>	6
<b>GLAND TYPE</b>	Non-armoured
<b>PROTECTION TYPE</b>	Industrial
<b>THREAD SIZE</b>	PG 11
<b>NOMINAL THREAD SIZE METRIC/PG</b>	11
<b>PITCH THREAD</b>	1.411 mm
<b>THREAD LENGTH</b>	6.5 mm
<b>WRENCH WIDTH</b>	24 mm
<b>HEXAGON ANGULAR DIMENSION</b>	26.4 mm
<b>SUITABLE FOR CABLE DIAMETER - MAX</b>	13 mm
<b>SUITABLE FOR CABLE DIAMETER - MIN</b>	6 mm
<b>MATERIAL QUALITY</b>	Brass
<b>SURFACE PROTECTION</b>	Nickel-plated
<b>DEGREE OF PROTECTION (IP)</b>	IP66
<b>MODEL</b>	Straight
<b>TYPE OF SEALING</b>	Sealing ring
<b>WORKING TEMPERATURE - MAX</b>	80 °C
<b>WORKING TEMPERATURE - MIN</b>	-20 °C
<b>FOR EX-ZONE GAS</b>	None
<b>FOR EX-ZONE DUST</b>	None
<b>FITTED WITH:</b>	Strain Relief Separable Screw Gland
<b>INTEGRATED FUNCTION</b>	Screened
<b>LAMP TYPE INCLUDED</b>	Halogen Free
<b>THREAD TYPE</b>	PG
<b>SUITABLE FOR</b>	Armoured Cable
<b>VERSION</b>	EMC

□□

□□□□	<a href="#">Cable management solutions for OEMs</a>
□□□□	<a href="#">Oil and Gas Global catalogue</a>
□□□□	<a href="#">eaton-moem-solutions-catalogue-capri-en-gb.pdf</a>

