



□□□□□

Eaton

BA80A0206A01100000

Eaton 93PS UPS, 8 kVA, 8 kW scalable to 20 kW, 1 x 15 kW power module, No battery, Network card included

□□□□

PRODUCT NAME	Eaton 91PS and 93PS UPS
CATALOG NUMBER	BA80A0206A01100000
PRODUCT LENGTH/DEPTH	33.5 cm
PRODUCT HEIGHT	130 cm
PRODUCT WIDTH	75 cm
PRODUCT WEIGHT	100 kg
COMPLIANCES	CE Marked RoHS Compliant CB
CERTIFICATIONS	IEC/EN 62040-2 IEC/EN 62040-1 EN 62040-3 Manufactured in a plant certified to ISO 9001 and ISO 14001 management system standards



Powering Business Worldwide

0000

AUDIBLE ALARMS	Yes
AUTO SHUTDOWN FUNCTION	Yes
BATTERY CHARGER TYPE	ABM technology
EXTERNAL BATTERY CONNECTION	Hardwired
COLOR	Black
CONSTRUCTION TYPE	Free standing model
EFFICIENCY (ECO-MODE)	99 %
IMPROVED EFFICIENCY MODE	ESS with VMMS
FEED TYPE	AC
FORM FACTOR	Tower
HOT-SWAPPABLE POWER MODULES	No
INPUT CONNECTION	Fixed connection
INPUT NOMINAL VOLTAGE	400V default (380/400/415V)
NUMBER OF OUTPUT CONNECTIONS FIXED CONNECTION	1
OUTPUT FREQUENCY	50 Hz (50/60 Hz programmable)
OUTPUT POWER FACTOR	1
OVERALL EFFICIENCY	96 %
PACKAGE CONTENTS	• UPS • Quickstart guide • Safety instructions
PARALLELEABLE	Parallel for capacity and redundancy
PHASE (INPUT)	3
PHASE (OUTPUT)	3
POTENTIAL FREE SWITCH CONTACT	Yes
SNMP	Yes
TOPOLOGY	Online
TYPE OF INTERFACE	Other
INTERNAL MAINTENANCE BYPASS	No
KVA RATING	8 kVA
WATTAGE	8 kW
APPLICATION	Data center/ facility/IT
OUTPUT EFFECTIVE POWER	8000 W

00

PEP ECO-PASSPORT

[eaton-small-ups-0-100kVA-pep-eato-00076-v0201-en.pdf](#)

[eaton-small-ups-pep-eato-00479-v0101-en.pdf](#)

TRANSITION TIME FOR FULL LOAD	0 s
EFFICIENCY (IMPROVED EFFICIENCY MODE)	99 %
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	1.5 %
INTEGRATED FUNCTIONALITY	Network Mangement Modular
INPUT FREQUENCY - MIN	50 Hz
INPUT FREQUENCY - MAX	60 Hz
INPUT VOLTAGE - MIN	380 V
INPUT VOLTAGE - MAX	415 V
OUTPUT VOLTAGE - MIN	380 V
OUTPUT VOLTAGE - MAX	415 V
SECONDARY FREQUENCY MIN	50 Hz
SECONDARY FREQUENCY MAX	60 Hz
OUTPUT APPARENT POWER	8000 VA
PRIMARY FREQUENCY - MAX	60 Hz
PRIMARY FREQUENCY - MIN	50 Hz
RUNTIME AT HALF LOAD	0 min
RUNTIME AT FULL LOAD	0 min
MOUNTING METHOD	Tower

□□□□:
□□□□:
□□□:
□□: