



Eaton CAP616204

Eaton Crouse-Hinds series Capri ISOCAP cable gland, Straight, Gland size 7, Non-armoured, Nickel plated brass, 8.5-13.5 outer sheath, Industrial, M20 Metric



PRODUCT NAME	Eaton's Crouse-Hinds series Capri ISOCAP cable gland
CATALOG NUMBER	CAP616204
PRODUCT LENGTH/DEPTH	21 mm
PRODUCT HEIGHT	24.25 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	18.8 g



Powering Business Worldwide

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	IEC
INGRESS PROTECTION (IP) RATINGS	IP66
MATERIAL	Nickel plated brass
CONNECTOR TYPE	Straight
GLAND SIZE	7
GLAND TYPE	Non-armoured
OUTER SHEATH (MIN/MAX)	8.5-13.5
PROTECTION TYPE	Industrial
THREAD SIZE	M20
NOMINAL THREAD SIZE METRIC/PG	20
PITCH THREAD	1.5 mm
THREAD LENGTH	6 mm
WRENCH WIDTH	22 mm
HEXAGON ANGULAR DIMENSION	24.2 mm
SUITABLE FOR CABLE DIAMETER - MAX	13.5 mm
SUITABLE FOR CABLE DIAMETER - MIN	8 mm
MATERIAL QUALITY	Brass
SURFACE PROTECTION	Nickel-plated
DEGREE OF PROTECTION (IP)	IP65
MODEL	Straight
TYPE OF SEALING	Sealing ring
WORKING TEMPERATURE - MAX	70 °C
WORKING TEMPERATURE - MIN	-5 °C
FOR EX-ZONE GAS	None
FOR EX-ZONE DUST	None
FITTED WITH:	Separable Screw Gland Strain Relief
THREAD TYPE	Metric

