



□□□□

Eaton

BC51A0206A01100000

Eaton 93PS UPS, 15 kVA, 15 kW scalable to 40 kW, 1 x 15 kW power module, No battery, Network card included

□□□□

PRODUCT NAME	Eaton 91PS and 93PS UPS
CATALOG NUMBER	BC51A0206A01100000
PRODUCT LENGTH/DEPTH	48 cm
PRODUCT HEIGHT	175 cm
PRODUCT WIDTH	75 cm
PRODUCT WEIGHT	152 kg
COMPLIANCES	CE Marked RoHS Compliant CB
CERTIFICATIONS	IEC/EN 62040-2 IEC/EN 62040-1 EN 62040-3 Manufactured in a plant certified to ISO 9001 and ISO 14001 management system standards



Powering Business Worldwide



AUDIBLE ALARMS	Yes
AUTO SHUTDOWN FUNCTION	Yes
BATTERY CHARGER TYPE	ABM technology
EXTERNAL BATTERY CONNECTION	Hardwired
COLOR	Black
CONSTRUCTION TYPE	Free standing model
EFFICIENCY (ECO-MODE)	99 %
IMPROVED EFFICIENCY MODE	ESS with VMMS
FEED TYPE	AC
FORM FACTOR	Tower
HOT-SWAPPABLE POWER MODULES	No
INPUT CONNECTION	Fixed connection
INPUT NOMINAL VOLTAGE	400V default (380/400/415V)
NUMBER OF OUTPUT CONNECTIONS FIXED CONNECTION	1
OUTPUT FREQUENCY	50 Hz (50/60 Hz programmable)
OUTPUT POWER FACTOR	1
OVERALL EFFICIENCY	96 %
PACKAGE CONTENTS	<ul style="list-style-type: none">• UPS• Quickstart guide• Safety instructions
PARALLELEABLE	Parallel for capacity and redundancy
PHASE (INPUT)	3
PHASE (OUTPUT)	3
POTENTIAL FREE SWITCH CONTACT	Yes
SNMP	Yes
TOPOLOGY	Online
TYPE OF INTERFACE	Other
INTERNAL MAINTENANCE BYPASS	No
KVA RATING	15 kVA
WATTAGE	15 kW
APPLICATION	Data center/ facility/IT
OUTPUT EFFECTIVE POWER	15000 W



PEP ECO-PASSPORT

[eaton-small-ups-0-100kVA-pep-eato-00076-v0201-en.pdf](#)

[eaton-small-ups-0-100kVA-pep-eato-00087-v0201-en.pdf](#)
