



□□□□□

Eaton BC63M100

Eaton Bussmann series low voltage british standard fuse, 63 A, AC 500 V, 21 x 114 mm, gM, 63M100

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	BC63M100
UPC	051712578479
PRODUCT LENGTH/DEPTH	3.302 mm
PRODUCT HEIGHT	21.082 mm
PRODUCT WIDTH	113.538 mm
PRODUCT WEIGHT	60.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 BS88

□□□□

AMPERAGE RATING	63 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	97.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	63M100
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	250 V
CLASS	Class gM
FUSE TYPE	BC
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.4 W
CONNECTION	97 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC AC/DC
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

