


Eaton BP192V12RT3US

192V External Battery Pack for Select Tripp Lite
UPS Systems, 3U Rack/Tower

PRODUCT NAME	Eaton Tripp Lite series battery pack
CATALOG NUMBER	BP192V12RT3US
UPC	037332238610
PRODUCT LENGTH/DEPTH	33 in
PRODUCT HEIGHT	11 in
PRODUCT WIDTH	23 in
PRODUCT WEIGHT	174 lb
COMPLIANCES	RoHS CE Marked
CERTIFICATIONS	CSA Std. C22.2 IEC/EN 62040-1 UL 1778

RACK SIZE	3U
PACKAGE CONTENTS	• BP192V12RT3US 192V External Battery Pack, 3U Rack/Tower • Smart battery communication cable • 4-post rack-mounting hardware • Owner's manual
SYSTEM REQUIREMENTS	5kVA and 6kVA SmartOnline Unity Power Factor UPS systems only: SU5KRT3UG, SU5KRT3UHV, SU5KRT3UHW, SU5KRT3UTF, SU5KRT3UX, SU6KRT3UG, SU6KRT3UHV, SU6KRT3UHW, SU6KRT3UTF, SU6KRT3UX, SU5KRT3UGMB, SU5KRT3UHVMB, SU5KRT3UHWMB, SU5KRT3UTFMB, SU6KRT3UGMB, SU6KRT3UHVMB, SU6KRT3UHWMB, SU6KRT3UTFMB, SU6KRT3UXMB and other UPS systems that specify the use of this battery pack
PRODUCT FEATURES	Expandable Runtime
PRODUCT HIGHLIGHTS	2-year limited warranty (U.S. and Canada -- warranties may vary by country) Smart pack communicates with UPS to automatically report battery temperature, accurate runtime, etc. Daisy-chain connector supports additional battery packs for even longer runtime Mounts in 3U of space in 19 in. rack using included 4-post installation hardware Supports 2-post rack or tower installation with optional accessories (sold separately) Connects to compatible 5kVA/6kVA Unity PF UPS systems for extended runtime
TAA COMPLIANCE	No
BATTERY RUNTIME	Expandable Runtime
TYPICAL BATTERY LIFE	4-6 years typical (North America)
DC VOLTAGE	192
MATERIAL OF CONSTRUCTION	Steel
MINIMUM REQUIRED RACK DEPTH	31 in
OVERLOAD PROTECTION	50A DC output fuse



UPS INPUT CORD LENGTH	3 ft
OPTIONAL ACCESSORIES	2 post rackmount (2POSTRMKITHD) Tower (2-9USTAND)

:
:
:
: