



□□□□□

Eaton DU101-0262

Eaton DU Duplex Low Pressure Filter,
DU101.25G.16.E.P.-.FS.6.-.-.OE2.2,5.B.-.P.-.,
25 G, Stainless steel wire mesh (G), Nitrile,
464 psi (32 Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU101-0262
PRODUCT LENGTH/DEPTH	295.17 mm
PRODUCT HEIGHT	463 mm
PRODUCT WIDTH	260.02 mm
PRODUCT WEIGHT	23.13 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

0000	
CONNECTION TYPE	1 1/4" SAE/ANSI flange
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	25 G
FILTER MEDIA TYPE	Stainless steel wire mesh (G)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	232 psi (16 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

