



## Eaton EAD32BH30C-A

Eaton Moeller series xPole - eRB6/M RCBO - residual-current circuit breaker with overcurrent protection. Electronic RCD/MCB, 32A, 30mA, MCB char. curve: B, 1p, RCCB trip char.: A, 6kA, A

### □□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - eRB6/M RCBO - residual-current circuit breaker with overcurrent protection
<b>CATALOG NUMBER</b>	EAD32BH30C-A
<b>PRODUCT LENGTH/DEPTH</b>	216 mm
<b>PRODUCT HEIGHT</b>	72 mm
<b>PRODUCT WIDTH</b>	17.5 mm
<b>PRODUCT WEIGHT</b>	0.18 kg
<b>COMPLIANCES</b>	CE Marked RoHS conform
<b>CERTIFICATIONS</b>	CE

## □□□□

**AMPERAGE RATING** 32 A

**VOLTAGE RATING** 240 V - 240 V

**SURGE CURRENT CAPACITY** 0.25 kA

**VOLTAGE TYPE** AC

**WIDTH IN NUMBER OF MODULAR SPACINGS** 1

### 10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

### 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

### 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

### 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

### 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

### 10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

## □□

[eaton-xpole-erb6-rcbo-catalog-ca019049en-en-us.pdf](#)

## □□□□

[eaton-xpole-erb6-au-rcbo-catalog-ca019052en-en-us.pdf](#)

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>OPERATING AMBIENT TEMPERATURE - MAX</b>	40 °C
<b>OPERATING AMBIENT TEMPERATURE - MIN</b>	-25 °C
<b>PRODUCT APPLICATION</b>	Switchgear for residential and commercial applications
<b>RATED CURRENT</b>	32 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	32 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W
<b>BUILT-IN DEPTH</b>	69.5 mm
<b>CURRENT LIMITING CLASS</b>	3
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)</b>	0 kA
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>FAULT CURRENT RATING</b>	0.03 A

<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>NUMBER OF POLES (PROTECTED)</b>	1
<b>NUMBER OF POLES (TOTAL)</b>	1
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	240 V
<b>BASIC FUNCTION</b>	Combined RCD/MCB devices
<b>MOUNTING METHOD</b>	DIN rail
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	10.7 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>DEGREE OF PROTECTION</b>	IP20
<b>OVERVOLTAGE CATEGORY</b>	III
<b>POLLUTION DEGREE</b>	2
<b>LEAKAGE CURRENT TYPE</b>	A
<b>RELEASE CHARACTERISTIC</b>	B
<b>FREQUENCY RATING</b>	50/60 Hz
<b>RATED INSULATION VOLTAGE (UI)</b>	500 V
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009)</b>	6 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN</b>	6 kA

61009-1)	
NUMBER OF POLES	Single-pole
DISCONNECTION CHARACTERISTIC	Undelayed
TYPE	RCBO
APPLICATION	Switchgear for residential and commercial applications
POWER LOSS	10.7 W
