

Eaton CD100M160

Eaton Bussmann series low voltage British standard fuse, Fuse-link, LV, 100 A, AC 415 V, BS88/B1, 26 x 126 mm, gM, BS, 100M160

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	CD100M160
UPC	051712838788
PRODUCT LENGTH/DEPTH	126 mm
PRODUCT HEIGHT	26 mm
PRODUCT WIDTH	26 mm
PRODUCT WEIGHT	107.7 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	160 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B1
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	100M160
RATED VOLTAGE AC	415 V
CLASS	Class gM
FUSE TYPE	CD
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	13 W
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B1
CONSTRUCTION SIZE	B1
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250891en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

