

Eaton EF400

Eaton Bussmann series low voltage british standard fuse, 400A, AC 415 V, V88/C1, 38 x 209 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	EF400
UPC	051712839761
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	39 mm
PRODUCT WIDTH	39 mm
PRODUCT WEIGHT	385 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

AMPERAGE RATING	400 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/C1
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	184 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	EF
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	29 W
CONNECTION	133/184 mm fixing centre
CONSTRUCTION	BS88/C1
CONSTRUCTION SIZE	C1
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	RS400 Red spot fuse holder
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250891en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

