


Eaton CH143DU

Eaton's Bussmann series 3-Pole modular fuse holder, rated at 690 V a.c./750 V d.c. (IEC), 700 V a.c. (UL), 50 Amps (IEC and UL), suitable for 14 x 51 mm Cylindrical fuses

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse holder
CATALOG NUMBER	CH143DU
UPC	051712685221
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	92 mm
PRODUCT WIDTH	80 mm
PRODUCT WEIGHT	262 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 EAC IEC 60269-1 UL Listed File E14853

USED WITH	C14G, C14M, FW-A14F fuses
AMPERAGE RATING	50 A
NUMBER OF POLES	Three-pole + N
WIDTH IN NUMBER OF MODULAR SPACINGS	4.5
BUILT-IN DEPTH	51.5 mm
FUSE SIZE	14 x 51 mm
OPERATING TEMPERATURE DETAILS	-20°C to +70°C
VOLTAGE RATING AT AC	690 V a.c. (IEC) and 700 V a.c. (UL)
VOLTAGE RATING AT DC	750 V d.c. (IEC)
FUSE TYPE	C14G C14M
LOCKABLE	Yes
ACCESSORIES	JV-L Multipole connector kit, CH14-CTP IP20 Protection accessory, CH14-TPS Microswitch to work with CH143D(I)U
TORQUE RATING	Max 3.5 Nm
CONCURRENTLY SWITCHING N-NEUTRAL	No
MATERIAL	Polyester
OPTICAL DEFECT INDICATION	No
MOUNTING METHOD	DIN rail 2 x M4 Panel mounting screws
DEGREE OF PROTECTION	IP20
VOLTAGE RATING	690 V
TYPE	Fuse holder
APPLICATION	Industrial and Commercial applications
MODEL	CH14



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

