



□□□□

## Eaton EP-400214

Eaton Moeller series SLC Signal tower compact, Green, Yellow, Red, 230 V AC, Standard mounting

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series SLC Signal tower compact
<b>CATALOG NUMBER</b>	EP-400214
<b>PRODUCT LENGTH/DEPTH</b>	70 mm
<b>PRODUCT HEIGHT</b>	291 mm
<b>PRODUCT WIDTH</b>	61 mm
<b>PRODUCT WEIGHT</b>	0.23 kg
<b>CERTIFICATIONS</b>	CE IEC/EN 60947-5-1 IEC/EN 60529 UL Category Control No.: NKCR, NKCR7 UL File No.: E29184 UL report applies to both US and Canada



Powering Business Worldwide



<b>TYPE</b>	Complete device
<b>PRODUCT CATEGORY</b>	SL signal towers
<b>FITTED WITH:</b>	Push-in
<b>POLLUTION DEGREE</b>	3
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>MOUNTING METHOD</b>	Standard stacklight base
<b>ILLUMINATION</b>	Continuous LED Red blinking LED
<b>BASE</b>	Standard
<b>DECIBEL</b>	0 dB
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>LEAKAGE CURRENT</b>	0.003 A
<b>OUTSIDE DIAMETER</b>	61 mm
<b>RADIATION ANGLE</b>	360 °
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	230 V
<b>RATED OPERATIONAL VOLTAGE (UE) - MIN</b>	230 V
<b>INRUSH CURRENT MAX.</b>	3.7 A
<b>COLOR</b>	Black tube Green Yellow Red
<b>LENS COLOR</b>	Green Yellow Red
<b>VOLTAGE TYPE</b>	AC
<b>MATERIAL</b>	UV Protected material
<b>MOUNTING POSITION</b>	As required
<b>DEGREE OF PROTECTION</b>	IP66 NEMA 4X
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CURRENT CONSUMPTION</b>	max. 21 mA at 230 V AC
<b>LIFESPAN, ELECTRICAL</b>	50,000 h
<b>LIGHT TYPE</b>	Continuous light Red blinking light
<b>LIGHT MODULES</b>	LED
<b>NUMBER OF MODULES</b>	1
<b>RATED OPERATIONAL VOLTAGE</b>	230 V AC



DECLARATIONS OF CONFORMITY

[eaton-signal-tower-compact-declaration-of-conformity-uk251129en.pdf](#)

