



□□□□

## Eaton DXX-NET-EIP

Eaton PowerXL DX1 Dual Port EIP Card

□□□□

<b>PRODUCT NAME</b>	Eaton PowerXL DX1 option card
<b>CATALOG NUMBER</b>	DXX-NET-EIP
<b>UPC</b>	786689880460
<b>PRODUCT LENGTH/DEPTH</b>	16 mm
<b>PRODUCT HEIGHT</b>	86 mm
<b>PRODUCT WIDTH</b>	54 mm
<b>PRODUCT WEIGHT</b>	0.033 kg
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide

**10.10 TEMPERATURE RISE**

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**AMBIENT OPERATING TEMPERATURE - MAX**

50 °C

**AMBIENT OPERATING TEMPERATURE - MIN**

-10 °C

**AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX**

50 °C

**AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN**

-30 °C

**AMBIENT STORAGE TEMPERATURE - MAX**

70 °C

**AMBIENT STORAGE TEMPERATURE - MIN**

-40 °C

**ALTITUDE**

Max. 1000 m  
 Max. 3000 m  
 Above 1000 m with 1 %  
 derating per 100 m  
 Max. 2000 m for Corner  
 Grounded TN Systems

**COMMUNICATION INTERFACE**

Ethernet IP

**ENVIRONMENTAL CLASS**

3C2, 3S2 (Air quality)

**NUMBER OF INPUTS (ANALOG)**

2

**OVERVOLTAGE CATEGORY**

III

**POLLUTION DEGREE**

2

**ACCESSORIES/SPARE PART TYPE**

Accessory  
 Communication module

