

Eaton ELSPSTR-N

Eaton Eluxa high fidelity speaker strobe,
LED, wall, red, no lettering, clear lens,
15/30/75/110/135/185 cd, 25/70V, indoor

PRODUCT NAME	Eaton Eluxa high fidelity speaker strobe
CATALOG NUMBER	ELSPSTR-N
UPC	786697010422
PRODUCT LENGTH/DEPTH	6.35 in
PRODUCT HEIGHT	2.94 in
PRODUCT WIDTH	4.56 in
PRODUCT WEIGHT	1.75 lb
COMPLIANCES	Not Applicable



TYPE	Speaker strobe
COMPLIANCE AND STANDARDS	UL ULC FCC
MOUNTING METHOD	Wall
HOUSING COLOR	Red
HOUSING MATERIAL	Plastic
LENS COLOR	Clear
LENS MATERIAL	Lexan
LAMP TYPE	LED

CURRENT DRAW (DC)	• 0.022 • 0.030 • 0.060 • 0.086 • 0.125 • 0.185
-------------------	---

FREQUENCY RANGE - MAX	8000 Hz
FREQUENCY RANGE - MIN	300 Hz
TAPS (SELECTABLE)	1/8, 1/4, 1/2, 1, 2
LETTERING	No lettering
OPERATING TEMPERATURE	32°F to 122°F (0°C to 50°C)
INDOOR/OUTDOOR	Indoor
CANDELA SETTINGS	15 cd 30 cd 75 cd 110 cd 135 cd 185 cd
TYPE OF SPEAKER	High fidelity
VOLTAGE	24 V 25 V 70 V
SOUND LEVEL (DBA)	75/79/82/85/87



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

