



Eaton ELSPSTW-NA

Eaton Eluxa high fidelity speaker strobe, LED, wall, white, no lettering, amber lens, 15/30/75/110/135/185 cd, 25/70V, indoor

□□□□

PRODUCT NAME	Eaton Eluxa high fidelity speaker strobe
CATALOG NUMBER	ELSPSTW-NA
UPC	786697010453
PRODUCT LENGTH/DEPTH	6.35 in
PRODUCT HEIGHT	2.94 in
PRODUCT WIDTH	4.56 in
PRODUCT WEIGHT	1.75 lb
COMPLIANCES	Not Applicable



Powering Business Worldwide

□□□□

□□

TYPE	Speaker strobe
COMPLIANCE AND STANDARDS	UL ULC FCC
MOUNTING METHOD	Wall
HOUSING COLOR	White
HOUSING MATERIAL	Plastic
LENS COLOR	Amber
LENS MATERIAL	Lexan
LAMP TYPE	LED
CURRENT DRAW (DC)	<ul style="list-style-type: none"> • 0.022 • 0.030 • 0.060 • 0.086 • 0.125 • 0.185
FREQUENCY RANGE - MAX	8000 Hz
FREQUENCY RANGE - MIN	300 Hz
TAPS (SELECTABLE)	1/8, 1/4, 1/2, 1, 2
LETTERING	No lettering
OPERATING TEMPERATURE	32°F to 122°F (0°C to 50°C)
INDOOR/OUTDOOR	Indoor
CANDELA SETTINGS	15 cd 30 cd 75 cd 110 cd 135 cd 185 cd
TYPE OF SPEAKER	High fidelity
VOLTAGE	24 V 25 V 70 V
SOUND LEVEL (DBA)	75/79/82/85/87

