



Eaton EP-401535

Eaton S711 Soft starter, 35 A, 200 - 575 V AC, Us= 24 V DC, with control unit, Frame size 1, IP20

□□□□

PRODUCT NAME	Eaton S711 soft starter
CATALOG NUMBER	EP-401535
PRODUCT LENGTH/DEPTH	252 mm
PRODUCT HEIGHT	174 mm
PRODUCT WIDTH	128 mm
PRODUCT WEIGHT	3.6 kg
CERTIFICATIONS	CE

DECLARATIONS OF
CONFORMITY

[eaton-soft-starter-
declaration-of-conformity-
uk251135en.pdf](#)

TYPE	Soft starter for three-phase loads, with control unit and pump algorithm, DC Brake, Soft Brake, Jog, Bluetooth
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Display Motor overload protection Internal bypass
POLLUTION DEGREE	3
CLASS	Adjustable
CLIMATIC PROOFING	5 to 95% Relative Humidity
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V
FRAME SIZE	FS1
ALTITUDE	Max 4000 m (Above 1000 m for detailed derating use S711 Select Software)
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	10 HP
ASSIGNED MOTOR	10 HP

POWER AT 220/230 V, 60 HZ, 3-PHASE	
ASSIGNED MOTOR	
POWER AT 460/480 V, 60 HZ, 3-PHASE	20 HP
ASSIGNED MOTOR	
POWER IN-DELTA AT 220/230 V, 60 HZ	15 HP
ASSIGNED MOTOR	
POWER IN-DELTA AT 460/480 V, 60 HZ	30 HP
ASSIGNED MOTOR	
POWER IN-DELTA AT 575/600 V, 60 HZ	40 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	
	144 W
HEAT DISSIPATION CAPACITY PDISS	
	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	
	0 W
MAINS VOLTAGE - MAX	
	632.5 V
MAINS VOLTAGE - MIN	
	170 V
OUTPUT VOLTAGE	
	250 V AC (relay outputs)
NUMBER OF OUTPUTS	
	3 Relay Outputs (1 fixed, 2 programmable)
VOLTAGE TYPE	
	DC
RATED OPERATIONAL VOLTAGE (UE) - MIN	
	200 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	
	575 V
RATED POWER THREE-PHASE MOTOR, INLINE, AT 230 V	
	7.5 kW
RATED POWER THREE-PHASE MOTOR, INLINE, AT 400 V	
	15 kW
RATED POWER THREE-PHASE MOTOR, INSIDE DELTA, AT 230 V	
	15 kW
RATED POWER THREE-PHASE MOTOR, INSIDE DELTA, AT 400 V	
	22 kW
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	
	35 W
VOLTAGE RATING - MAX	
	575 V

APPLICATION	<ul style="list-style-type: none"> • 3-phase motors: Yes • Soft starting of three-phase asynchronous motors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact
MOUNTING POSITION	As required
DROP-OUT VOLTAGE	0 - 16 V, DC operated
DEGREE OF PROTECTION	IP20 NEMA 1
FUNCTIONS	Single direction Torque control DC-Brake Soft-Brake Forward & reverse jog
OVERLOAD CYCLE	AC-53b: 3.5-20:340
PICK-UP VOLTAGE	19.2 - 28.8 V DC
RADIO INTERFERENCE CLASS	Class A (IEC 60947-4-2)
FAULT MEMORY	1000 Faults
INTERFACES	Modbus RTU (built-in) Bluetooth (built-in)
KICKSTART	600% (Kickstart current) Max. 2000 ms (Kickstart Duration)
RATED CONTROL VOLTAGE (UC)	24 V DC (-20 %/+20 %)
SUPPLY FREQUENCY	50/60 Hz, fLN, Main circuit
TERMINAL CAPACITY (STRANDED)	1 x (6 - 70) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	24 VDC
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	24 VDC
RATED INSULATION VOLTAGE (UI)	600 V
RATED OPERATIONAL CURRENT (IE) AT AC-11	3 A
RATED OPERATIONAL CURRENT (IE) AT AC-53	32 A
RATED OPERATIONAL CURRENT (IE) AT AC-53, IN-DELTA	48 A

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	32 A
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER AT 400 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT 500 V, 50 HZ	22 kW
RATED OPERATIONAL POWER IN-DELTA AT 220/230 V, 50 HZ	15 kW
RATED OPERATIONAL POWER IN-DELTA AT 400 V, 50 HZ	22 kW
RATED OPERATIONAL POWER IN-DELTA AT 500 V, 50 HZ	30 kW
RATED OPERATIONAL VOLTAGE (UE) - MAX	575 V
RAMP/RUN-UP TIME	180 s
SHOCK RESISTANCE	15 g, Mechanical
TIGHTENING TORQUE	0.5 Nm, Screw terminals, Control circuit cables 4 Nm, Main cables
START VOLTAGE	Max. 600% FLA, Min. 100% FLA, Soft start function
STARTUP CLASS	CLASS 20 (heavy starting duty 3 x I _e for 45 s) CLASS 10 (star-delta replacement) CLASS 30 (6 x I _e for 30 s)
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (6 - 70) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID)	1 x (6 - 70) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	1 x (10 - 2/0), Main cables 1x (28 - 12) , Control circuit cables

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

