

Eaton EP-501353

EMC2-H311/55-W/BF4 . Floor-standing distribution board EMC2 pre-assembled, IP55, protection class II, HxWxD=1700x800x270mm, white (RAL 9016)

PRODUCT NAME	Eaton xEnergy Basic EMC2 enclosure pre-assembled
CATALOG NUMBER	EP-501353
PRODUCT LENGTH/DEPTH	270 mm
PRODUCT HEIGHT	1800 mm
PRODUCT WIDTH	800 mm
PRODUCT WEIGHT	74 kg
CERTIFICATIONS	CE



FEATURES	EMC-version Connectable
FITTED WITH:	Door
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IP55 IK10 Other
MATERIAL QUALITY	Other
COLOR	White
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	880 N
NUMBER OF LOCKS	0
RAL-NUMBER	9016
MATERIAL	Steel
MOUNTING METHOD	Wall mounting
INSTALLATION TYPE	Floor standing wall model
NUMBER OF COVERS/DOORS	2
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	2000 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	100 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	160 W
NUMBER OF CONNECTOR HOLES	0



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

