



□□□□

## Eaton EP-501544

Eaton Moeller series IZMY/INY Circuit-breaker, 3 pole, 400 A, 50 kA, Power loss: 12 W, Selective operation, IEC, Fixed

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series IZMY/INY circuit-breaker
<b>CATALOG NUMBER</b>	EP-501544
<b>PRODUCT LENGTH/DEPTH</b>	248 mm
<b>PRODUCT HEIGHT</b>	315 mm
<b>PRODUCT WIDTH</b>	200 mm
<b>PRODUCT WEIGHT</b>	25 kg
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide



<b>FEATURES</b>	Complete device with protection unit Motor drive optional
<b>FITTED WITH:</b>	Switched-off indicator
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	400 A
<b>DEVICE CONSTRUCTION</b>	Built-in device fixed built-in technique
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Rail connection
<b>ACTUATOR TYPE</b>	Push button
<b>ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX</b>	4000 A
<b>ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN</b>	240 A
<b>ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX</b>	6000 A
<b>ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MIN</b>	800 A
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	4
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>OVERLOAD RELEASE CURRENT SETTING - MAX</b>	400 A
<b>OVERLOAD RELEASE CURRENT SETTING - MIN</b>	160 A
<b>NUMBER OF POLES</b>	Three-pole
<b>DEGREE OF PROTECTION</b>	IP20
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Back side
<b>RATED OPERATING VOLTAGE (UE) - MAX</b>	690 V
<b>RATED OPERATING VOLTAGE (UE) - MIN</b>	690 V
<b>RATED SHORT-CIRCUIT</b>	50 kA



MCAD MODEL	<a href="#">eaton-acb-sd-mcad-3d-models-izmy16-3p-fixed.stp</a>
------------	---

