

Eaton ESD63M80

Eaton Bussmann series low voltage british standard fuse, 80 A, AC 415 V, V88/F2, 21 x 68 mm, gM, 63M80

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	ESD63M80
UPC	051712844611
PRODUCT LENGTH/DEPTH	22 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	42.15 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	80 A
FITTED WITH:	Offset bladed tags
FUSE SIZE	BS88/F2
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	63M80
RATED VOLTAGE AC	415 V
CLASS	Class gM
FUSE TYPE	ESD
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.4 W
CONNECTION	Blade end
CONSTRUCTION	BS88/F2
CONSTRUCTION SIZE	F2
FUSE SHAPE	Offset bladed tags
VOLTAGE TYPE	AC
SUITABLE FOR	63ENS Safeloc fuse holder SC63 Safeclip fuse holder
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250973en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

