

Eaton EP-400984

Eaton Moeller® series P3 Main switch, 80 A, Surface mounting, 3 pole, Form I5/SVB, Red, Door coupling rotary drive, HI11

PRODUCT NAME	Eaton Moeller® series P3 Main switch
CATALOG NUMBER	EP-400984
PRODUCT LENGTH/DEPTH	169 mm
PRODUCT HEIGHT	180 mm
PRODUCT WIDTH	200 mm
PRODUCT WEIGHT	1.54 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	VDE EN 60947-3 IEC 60947 UL 508 CSA Std. C22.2 No. 14-05 UL CSA IEC/EN 60947 IEC/EN 60204 IEC/EN 60947-3 VDE 0660

PRODUCT CATEGORY	Main switch
FEATURES	Version as emergency stop installation Version as maintenance-/service switch Version as main switch Version as safety switch
ACTUATOR COLOR	Red
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Red rotary handle and yellow locking ring
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
RATED PERMANENT CURRENT AT AC-21, 400 V	80 A
RATED PERMANENT CURRENT AT AC-23, 400 V	80 A
RATED UNINTERRUPTED CURRENT (IU)	80 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W

PVS	
SWITCHING ANGLE	90 °
SWITCHING POWER AT 400 V	55 kW
VOLTAGE PER CONTACT PAIR IN SERIES	60 V
ACCESSORIES	Auxiliary contact or neutral conductor fitted by user.
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	45 kW
DEVICE CONSTRUCTION	Complete device in housing
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	2 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
MOUNTING POSITION	As required
ACTUATOR TYPE	Door coupling rotary drive
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	10 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	15 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	20 HP
ASSIGNED MOTOR	50 HP

POWER AT 460/480 V, 60 HZ, 3-PHASE	
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	60 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	7.5 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	7.5 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	1
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	4 kA (Load side) 80 kA (Supply side)
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	Three-pole
MOUNTING METHOD	Surface mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Ground mounting
LOCKING FACILITY	Lockable in the 0 (Off) position
FUNCTIONS	Interlockable Emergency switching off function
NUMBER OF SWITCHES	1
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
SCREW SIZE	M5, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

LIFESPAN, MECHANICAL	100,000 Operations
LOAD RATING	1.3 x I _e (with intermittent operation class 12, 60 % duty factor) 2 x I _e (with intermittent operation class 12, 25 % duty factor) 1.6 x I _e (with intermittent operation class 12, 40 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	P600 (UL/CSA) A600 (UL/CSA)
TERMINAL CAPACITY	14 - 2 AWG, solid or flexible with ferrule 1 x (2.5 - 35) mm ² , solid or stranded 1 x (1.5 - 25) mm ² , flexible with ferrules to DIN 46228 2 x (1.5 - 6) mm ² , flexible with ferrules to DIN 46228 2 x (2.5 - 10) mm ² , solid or stranded
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	100 A, If used with neutral conductor IU = max. 90 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2
NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	2
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	760 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	740 A
RATED BREAKING	880 A

CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	520 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	950 A
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	10 kA, SCCR (UL/CSA) 150A, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING	100 A gG/gL, Fuse, Contacts
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	80 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	68 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	71 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	71 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	65 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	23.8 A
RATED OPERATIONAL CURRENT (IE) AT DC-1,	80 A

LOAD-BREAK SWITCHES	
L/R = 1 MS	
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	50 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	80 A
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	30 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	30 kW
TIGHTENING TORQUE	26.5 lb-in, Screw terminals 3 Nm, Screw terminals
UNINTERRUPTED CURRENT	Rated uninterrupted current I _u is specified for max. cross-section.
RATED SWITCHING CAPACITY	10 HP at 200 V AC, single-phase 15 HP at 240 V AC, single-phase 20 HP at 200 V AC, three-phase 25 HP at 240 V AC, three-phase 5 HP at 120 V AC, single-phase 60 HP at 480 V AC, three-phase 75 HP at 600 V AC, three-phase
HOUSING COLOR	Gray
HOUSING MATERIAL	Plastic

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

