



## Eaton FG450

Eaton Bussmann series low voltage british standard fuse, 450A, AC 550 V, DC 400 V, 74 x 262 mm, gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	FG450
<b>UPC</b>	051712844918
<b>PRODUCT LENGTH/DEPTH</b>	27.4 mm
<b>PRODUCT HEIGHT</b>	8 mm
<b>PRODUCT WIDTH</b>	7.8 mm
<b>PRODUCT WEIGHT</b>	1.2 kg
<b>COMPLIANCES</b>	RoHS Compliant



Powering Business Worldwide



<b>AMPERAGE RATING</b>	450 A
<b>FITTED WITH:</b>	Centre bolted tags
<b>CURRENT TYPE</b>	AC/DC
<b>MOUNTING DIMENSION</b>	M10
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	231 mm
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>RATED VOLTAGE AC</b>	550 V
<b>RATED VOLTAGE DC</b>	400 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	FG
<b>UTILIZATION CATEGORY</b>	gG (cable protection/equipment protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	32 W
<b>CONNECTION</b>	167/231 mm fixing centre
<b>CONSTRUCTION</b>	BS88
<b>CONSTRUCTION SIZE</b>	Other
<b>FUSE SHAPE</b>	Center bolted tags
<b>VOLTAGE TYPE</b>	AC/DC
<b>VOLTAGE RATING</b>	550 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other



DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250892en.pdf](#)

