



Eaton FT1SU250WLS13IP

Eaton FlexiTech, Safety light 1, Uniform illumination, 250lm, WLS, 1 to 3H, IP66

□□□□

PRODUCT NAME	Eaton FlexiTech SU SC safety luminaire
CATALOG NUMBER	FT1SU250WLS13IP
PRODUCT LENGTH/DEPTH	231 mm
PRODUCT HEIGHT	34 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.33 kg
CERTIFICATIONS	CE

BATTERY QUALITY	Lithium-ion
PROTECTION CLASS	II
DEGREE OF PROTECTION	IP66
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	Yes
LAMP HOLDER	None
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
POWER FACTOR	0.4
WITH REMOTE SWITCH CONNECTION	No
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	2 W
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	45 °C
NOMINAL OPERATION TIME - MIN	3 hour
NOMINAL OPERATION TIME - MAX	1 hour
SUITABLE FOR STANDBY SWITCHING	No
SUITABLE FOR CONTINUOUS CIRCUIT	No
RAL-NUMBER (SIMILAR) HOUSING	9003
MOUNTING METHOD	Wall surface mounted / ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White

MATERIAL COVER	Plastic, transparent
PICTOGRAM INCLUDED	No
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK07
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	250 lm
COLOR TEMPERATURE - MAX	6500 K
COLOR TEMPERATURE - MIN	6500 K
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
FUNCTION	Escape route lighting
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	No
LUMINOUS FLUX IN STANDBY MODE	100 lm
NUMBER OF LIGHTING HEADS	1
PRODUCT BRANDING	Eaton
WITH REMOTE CONTROL	No
CONSTANT LIGHT OUTPUT (CLO)	No
EXCHANGEABLE CONTROL GEAR	No
