



□□□□

## Eaton FT2CW4IUCGL18IP

Eaton FlexiTech, Combined Wall, 20m, UP, 4 Pictogram (DRLU) Down Right Left Up, CGLine+, 1 to 8H, IP66

□□□□

<b>PRODUCT NAME</b>	Eaton FlexiTech CW SC emergency luminaire
<b>CATALOG NUMBER</b>	FT2CW4IUCGL18IP
<b>PRODUCT LENGTH/DEPTH</b>	231 mm
<b>PRODUCT HEIGHT</b>	138 mm
<b>PRODUCT WIDTH</b>	34 mm
<b>PRODUCT WEIGHT</b>	0.52 kg
<b>CERTIFICATIONS</b>	Not Applicable



Powering Business Worldwide

□□□□

□□

<b>BATTERY VOLTAGE</b>	3.2 V
<b>BATTERY QUALITY</b>	Lithium-ion
<b>GLOW WIRE TEST</b>	850 °C
<b>PERMISSIBLE AMBIENT TEMPERATURE - MIN</b>	0 °C
<b>PERMISSIBLE AMBIENT TEMPERATURE - MAX</b>	45 °C
<b>PROTECTION CLASS</b>	II
<b>OUTDOOR USE COMPLIANCE</b>	False
<b>EXPLOSION PROTECTED</b>	False
<b>PRODUCT FUNCTION</b>	Combined version
<b>DEGREE OF PROTECTION</b>	IP65
<b>MODE</b>	Maintained / Non-Maintained (M / NM)
<b>LAMP TYPE</b>	LED not exchangeable
<b>WITH LIGHT SOURCE</b>	True
<b>LAMP HOLDER</b>	None
<b>TYPE OF INDICATOR</b>	Only single-sided
<b>MONITORING EQUIPMENT</b>	Safety module for monitoring (central feeded system)
<b>POWER SUPPLY SYSTEM</b>	Peripheral (individual battery)
<b>VOLTAGE TYPE</b>	AC
<b>APPARENT POWER AT MAINS OPERATION</b>	3.7 VA
<b>POWER FACTOR</b>	0.43
<b>WIRING SYSTEM</b>	Continuous circuit/emergency circuit
<b>WITH REMOTE SWITCH CONNECTION</b>	True
<b>RESERVE-POLARITY PROTECTED</b>	True
<b>CONDUCTOR CROSS SECTION</b>	2.5
<b>CONNECTION TYPE</b>	Plug-in connection
<b>MAX. SYSTEM POWER</b>	1.6 W
<b>TYPE OF CONTROL GEAR</b>	Not required
<b>NOMINAL VOLTAGE AC - MAX</b>	230 V
<b>NOMINAL VOLTAGE AC - MIN</b>	230 V
<b>NOMINAL OPERATION TIME - MIN</b>	1 hour

<b>NOMINAL OPERATION TIME - MAX</b>	8 hour
<b>AUTONOMY</b>	1h
<b>ENERGY EFFICIENCY CLASS OF THE LIGHT SOURCE ACCORDING TO EU REGULATION 2019/2015</b>	A
<b>MOUNTING METHOD</b>	Wall surface mounted
<b>MATERIAL HOUSING</b>	Plastic
<b>COLOR HOUSING</b>	White
<b>MATERIAL COVER</b>	Plastic, transparent
<b>LIMITED SURFACE TEMPERATURE</b>	False
<b>LABELLING TYPE</b>	Insert sheet/plate
<b>PICTOGRAM INCLUDED</b>	True
<b>NUMBER OF POLES (NUMERIC)</b>	3
<b>IMPACT STRENGTH</b>	IK07
<b>KIND OF LUMINAIRE</b>	Safety and exit sign luminaire
<b>RATED LUMINOUS FLUX ACC. IEC 62722-2-1</b>	240 lm
<b>COLOR TEMPERATURE - MAX</b>	6500 K
<b>COLOR TEMPERATURE - MIN</b>	6500 K
<b>LIGHT DISTRIBUTOR</b>	Diffuser lens/optic/panel
<b>ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP</b>	A++, A+, A (LED)
<b>FUNCTION</b>	Escape route lighting/signage
<b>COLOR RENDERING INDEX (CRI)</b>	80
<b>LUMINOUS FLUX IN STANDBY MODE</b>	60 lm
<b>SUITABLE FOR NUMBER OF LAMPS</b>	2
<b>VIEWING DISTANCE</b>	20 m
<b>FREQUENCY</b>	50/60 Hz
<b>PRODUCT BRANDING</b>	Eaton
<b>SHAPE</b>	Rectangular
<b>APPLICATION</b>	Other
<b>TESTING SYSTEM</b>	CGLine +

