



□□□□

## Eaton EP-401308

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 4 kW, 1 NC, 48 V DC, DC operation, Push in terminals

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series DILM contactor
<b>CATALOG NUMBER</b>	EP-401308
<b>PRODUCT LENGTH/DEPTH</b>	75 mm
<b>PRODUCT HEIGHT</b>	68 mm
<b>PRODUCT WIDTH</b>	45 mm
<b>PRODUCT WEIGHT</b>	0.285 kg
<b>COMPLIANCES</b>	CE RoHS conform



Powering Business Worldwide

<b>NUMBER OF POLES</b>	Three-pole
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.

DECLARATIONS OF CONFORMITY

[eaton-contactor-declaration-of-conformity-uk251209en.pdf](#)

<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Mirror contact Built-in suppressor circuit
<b>OPERATING FREQUENCY</b>	9000 mechanical Operations/h (DC operated)
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>CONNECTION</b>	Push in terminals
<b>FRAME SIZE</b>	FS1
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>ASSIGNED MOTOR</b>	0.5 HP

<b>POWER AT 115/120 V, 60 HZ, 1-PHASE</b>	
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE</b>	3 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>	1.5 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE</b>	3 HP
<b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>	5 HP
<b>ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE</b>	7.5 HP
<b>CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)</b>	45 A
<b>CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)</b>	18 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)</b>	21 A
<b>CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)</b>	50 A
<b>SWITCHING TIME (DC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX</b>	12 ms
<b>APPLICATION</b>	Contactors for Motors
<b>PRODUCT CATEGORY</b>	Contactors
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
<b>ARCING TIME</b>	10 ms
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Push-in connection Spring clamp connection
<b>SCREWDRIVER SIZE</b>	3.0 x 0.5 mm, Terminal screw
<b>VOLTAGE TYPE</b>	DC
<b>DEGREE OF PROTECTION</b>	IP20
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1

<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
<b>NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)</b>	3
<b>POWER CONSUMPTION (PICK-UP) AT DC</b>	4.5 W
<b>POWER CONSUMPTION (SEALING) AT DC</b>	4.5 W
<b>RATED BREAKING CAPACITY AT 220/230 V</b>	90 A
<b>RATED BREAKING CAPACITY AT 380/400 V</b>	90 A
<b>RATED BREAKING CAPACITY AT 500 V</b>	70 A
<b>RATED BREAKING CAPACITY AT 660/690 V</b>	50 A
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DUTY FACTOR</b>	100 %
<b>EMITTED INTERFERENCE</b>	According to EN 60947-1
<b>INTERFERENCE IMMUNITY</b>	According to EN 60947-1
<b>LIFESPAN, MECHANICAL</b>	10,000,000 Operations (DC operated)
<b>PICK-UP VOLTAGE</b>	0.8 - 1.1 V DC x $U_c$ 0.85 - 1.1 V DC x $U_c$ (only with auxiliary contact module with 3 or more N/C contacts)
<b>SAFE ISOLATION</b>	400 V AC, Between coil and contacts, According to EN 61140 400 V AC, Between the contacts, According to EN 61140
<b>TERMINAL CAPACITY (FLEXIBLE WITH UNISOLATED FERRULE)</b>	1 x (0.5 - 2.5) mm <sup>2</sup> 2 x (0.5 - 2.5) mm <sup>2</sup>
<b>TERMINAL CAPACITY (FLEXIBLE WITH ULTRASONIC WELDED)</b>	1 x (0.5 - 2.5) mm <sup>2</sup> 2 x (0.5 - 2.5) mm <sup>2</sup>

<b>CABLE END)</b>	
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)</b>	1 A, 250 V DC, (UL/CSA) 10 A, 600 V AC, (UL/CSA)
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)</b>	P300, DC operated (UL/CSA) A600, AC operated (UL/CSA)
<b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>	1 x (0.5 - 2.5) mm <sup>2</sup> 2 x (0.5 - 1.5) mm <sup>2</sup>
<b>SHOCK RESISTANCE</b>	5.7 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 3.4 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 3.4 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
<b>TERMINAL CAPACITY (SOLID)</b>	1 x (0.5 - 2.5) mm <sup>2</sup> 2 x (0.5 - 2.5) mm <sup>2</sup>
<b>TERMINAL CAPACITY (SOLID/STRANDED AWG)</b>	20 - 14
<b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>	20 A, Maximum motor rating (UL/CSA)
<b>TERMINAL CAPACITY (FLEXIBLE)</b>	1 x (0.5 - 2.5) mm <sup>2</sup> 2 x (0.5 - 2.5) mm <sup>2</sup>
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	48 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	48 V

<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)</b>	126 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V</b>	22 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	9 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	9 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V</b>	9 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>	7 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	5 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V</b>	6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V</b>	6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V</b>	6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V</b>	5 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V</b>	4.5 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V</b>	20 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V</b>	20 A
<b>RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ</b>	3 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400</b>	4 kW

<b>V, 50 HZ</b>	
<b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>	5.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ</b>	1.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ</b>	1.6 kW
<b>RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ</b>	2.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ</b>	2.8 kW
<b>RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ</b>	3 kW
<b>RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ</b>	2.8 kW
<b>RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ</b>	3.6 kW
<b>RATED OPERATIONAL POWER (NEMA)</b>	3.7 kW
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>RESISTANCE PER POLE</b>	4.6 mΩ
<b>STRIPPING LENGTH (CONTROL CIRCUIT CABLE)</b>	10 mm
<b>STRIPPING LENGTH (MAIN CABLE)</b>	10 mm
<b>SHORT-CIRCUIT CURRENT RATING (BASIC RATING)</b>	5 kA, 30 A max. fuse, SCCR (UL/CSA) 5 kA, 30 A max. CB, SCCR (UL/CSA)
<b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)</b>	100 kA, 20 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA) 65 kA, 16 A max. CB, SCCR (UL/CSA)
<b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)</b>	100 kA, 20 A CLASS J max. fuse, SCCR (UL/CSA) 30 kA, 25 A CLASS RK5 max. fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION)</b>	35 A gG/gL

<b>AT 400 V</b>	
<b>SUITABLE FOR</b>	Also motors with efficiency class IE3
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V</b>	20 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V</b>	20 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V</b>	16 A gG/gL
<b>SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS</b>	18 A (480V 60Hz 3phase, 277V 60Hz 1phase) 18 A (600V 60Hz 3phase, 347V 60Hz 1phase)
<b>SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING</b>	54 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 9 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)
<b>SPECIAL PURPOSE RATING OF ELEVATOR CONTROL</b>	2 HP, 200 V 60 Hz 3-ph, (UL/CSA) 2 HP, 240 V 60 Hz 3-ph, (UL/CSA) 4.8 A, 480 V 60 Hz 3-ph, (UL/CSA) 7.8 A, 200 V 60 Hz 3-ph, (UL/CSA) 6.8 A, 240 V 60 Hz 3-ph, (UL/CSA) 3 HP, 480 V 60 Hz 3-ph, (UL/CSA) 5 HP, 600 V 60 Hz 3-ph, (UL/CSA) 6.1 A, 600 V 60 Hz 3-ph, (UL/CSA)
<b>SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY)</b>	10 A, FLA 480 V 60 Hz 3phase; (CSA) 10 A, FLA 600 V 60 Hz 3phase; (CSA) 60 A, LRA 480 V 60 Hz 3phase; (CSA) 60 A, LRA 600 V 60 Hz 3phase; (CSA)
<b>SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING</b>	18 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 18 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
<b>SPECIAL PURPOSE</b>	14 A, 480 V 60 Hz 3phase,

