



Eaton EP-401528

Eaton S711 Soft starter, 320 A, 200 - 575 V AC, Us= 110-240 V AC, with control unit, Frame size 4, IP00

□□□□

PRODUCT NAME	Eaton S711 soft starter
---------------------	-------------------------

CATALOG NUMBER	EP-401528
-----------------------	-----------

PRODUCT LENGTH/DEPTH	545 mm
-----------------------------	--------

PRODUCT HEIGHT	204 mm
-----------------------	--------

PRODUCT WIDTH	222 mm
----------------------	--------

PRODUCT WEIGHT	20.1 kg
-----------------------	---------

CERTIFICATIONS	CE RCM IEC/EN 60947-4-2 CUL UL UL 60947-4-2 UL Category Control No.: NMFT UL Category Control No.: NMFT7 UL File No.: E251034
-----------------------	---

DECLARATIONS OF
CONFORMITY

[eaton-soft-starter-
declaration-of-conformity-
uk251135en.pdf](#)

TYPE	Soft starter for three-phase loads, with control unit and pump algorithm, DC Brake, Soft Brake, Jog, Bluetooth
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Display Motor overload protection Internal bypass
POLLUTION DEGREE	3
CLASS	Adjustable Adjustable (5,10,15,20,30)
CLIMATIC PROOFING	5 to 95% Relative Humidity
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V
FRAME SIZE	FS4
ALTITUDE	Max 4000 m (Above 1000 m for detailed derating use S711 Select Software)
NUMBER OF INPUTS	5 (2 fixed, 2 programmable, 1 thermistor)
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C

ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	100 HP
ASSIGNED MOTOR POWER AT 220/230 V, 60 HZ, 3-PHASE	100 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	250 HP
ASSIGNED MOTOR POWER IN-DELTA AT 220/230 V, 60 HZ	150 HP
ASSIGNED MOTOR POWER IN-DELTA AT 460/480 V, 60 HZ	350 HP
ASSIGNED MOTOR POWER IN-DELTA AT 575/600 V, 60 HZ	450 HP
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	1440 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0 W
MAINS VOLTAGE - MAX	632.5 V
MAINS VOLTAGE - MIN	170 V
OUTPUT VOLTAGE	250 V AC (relay outputs)
NUMBER OF OUTPUTS	3 Relay Outputs (1 fixed, 2 programmable)
SCREWDRIVER SIZE	17 mm M10, Terminal screw, Main cables 0.6 x 3.5 mm or PH0, Terminal screws, Control circuit cables
VOLTAGE TYPE	AC
RATED OPERATIONAL VOLTAGE (UE) - MIN	200 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	575 V
RATED POWER THREE- PHASE MOTOR, INLINE, AT 230 V	90 kW
RATED POWER THREE- PHASE MOTOR, INLINE, AT 400 V	160 kW
RATED POWER THREE- PHASE MOTOR, INSIDE DELTA, AT 230 V	150 kW

RATED POWER THREE-PHASE MOTOR, INSIDE DELTA, AT 400 V	250 kW
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	140 W
VOLTAGE RATING - MAX	575 V
APPLICATION	<ul style="list-style-type: none"> • 3-phase motors: Yes • Soft starting of three-phase asynchronous motors
PROTECTION	Optional terminal cover for Finger and back-of-hand proof, Protection against direct contact
MOUNTING POSITION	As required
DROP-OUT VOLTAGE	0 - 90 V, AC operated
DEGREE OF PROTECTION	IP00 NEMA Other
CURRENT CONSUMPTION	600 mA, Control circuit, Digital inputs
FUNCTIONS	Single direction Torque control DC-Brake Soft-Brake Forward & reverse jog
OVERLOAD CYCLE	AC-53b: 3.5-20:580
PICK-UP VOLTAGE	93.5 - 264.0 V AC
RADIO INTERFERENCE CLASS	Class A (IEC 60947-4-2)
FAULT MEMORY	1000 Faults
INTERFACES	Modbus RTU (built-in) Bluetooth (built-in)
KICKSTART	600% (Kickstart current) Max. 2000 ms (Kickstart Duration)
RATED CONTROL VOLTAGE (UC)	110 - 240 V AC (-15%/+10%)
SUPPLY FREQUENCY	50/60 Hz, fLN, Main circuit
TERMINAL CAPACITY (STRANDED)	1 x (185 - 400) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	240 V
RATED CONTROL SUPPLY	110 V

VOLTAGE (US) AT AC, 50 HZ - MIN	
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED INSULATION VOLTAGE (UI)	600 V
RATED OPERATIONAL CURRENT (IE) AT AC-11	3 A
RATED OPERATIONAL CURRENT (IE) AT AC-53	320 A
RATED OPERATIONAL CURRENT (IE) AT AC-53, IN-DELTA	480 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	320 A
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ	90 kW
RATED OPERATIONAL POWER AT 400 V, 50 HZ	160 kW
RATED OPERATIONAL POWER AT 500 V, 50 HZ	220 kW
RATED OPERATIONAL POWER IN-DELTA AT 220/230 V, 50 HZ	150 kW
RATED OPERATIONAL POWER IN-DELTA AT 400 V, 50 HZ	250 kW
RATED OPERATIONAL POWER IN-DELTA AT 500 V, 50 HZ	315 kW
RATED OPERATIONAL VOLTAGE (UE) - MAX	575 V
RAMP/RUN-UP TIME	180 s
SHOCK RESISTANCE	15 g, Mechanical
SUITABLE FOR	Branch circuits, not as BCPD, (UL/cUL)
TIGHTENING TORQUE	0.5 Nm, Screw terminals, Control circuit cables 40 Nm, Main cables
START VOLTAGE	Max. 600% FLA, Min. 100% FLA, Soft start function
STARTUP CLASS	CLASS 20 (heavy starting duty 3 x I _e for 45 s) CLASS 10 (star-delta replacement)

	CLASS 30 (6 x I _e for 30 s)
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (185 - 400) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID)	1 x (185 - 400) mm ² , Main cables 1x (1 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	1 x (350 - 750), Main cables 1x (28 - 12) , Control circuit cables

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

